
ACCELERATE HD

HIGH-DENSITY SLIM BODY ARRAYS

(0.635 mm) .025" PITCH



FEATURES & BENEFITS


- Up to 400 positions in a 4-row design
- 5 mm, 7 mm, 9 mm, 10 mm, 11 mm, 12 mm 14 mm & 16 mm stack heights
- Slim 5 mm width body design
- Edge Rate® contact system optimized for signal integrity performance
- · Open-pin-field for grounding and routing flexibility
- Supports 64 Gbps PAM4 (32 Gbps NRZ) applications
- PCle® 6.0/CXL™ 3.1 capable





SureWare[™] ultra rugged guide post standoffs available (GPSO)

HIGHER DENSITY THAN PREVIOUS GENERATION STRIPS



KEY SPECIFICATIONS (ADM6/ADF6)

PITCH	TOTAL POSITIONS	INSULATOR MATERIAL	CONTACT MATERIAL	PLATING	OPERATING TEMP RANGE	CURRENT RATING	WORKING VOLTAGE	LEAD-FREE SOLDERABLE
(0.635 mm) .025"	40 - 400	Black LCP	Copper Alloy	Au or Sn over 50 μ" (1.27 μm) Ni	-55 °C to +125 °C	1.4 A per pin (4 pins powered)	155 VAC	Yes

PCI-SIG®, PCI Express® and the PCIe® design marks are registered trademarks and/or service marks of PCI-SIG.





(0.635 mm) .025" PITCH • SLIM BODY OPEN-PIN-FIELD ARRAYS



-50, -60, ADF6 (per row) Socket -70, -80,

-90, -100 (ADF6-03.5 & ADM6-01.5 lead styles only)


= 10 µ" (0.25 µm) Gold on contact area, Matte Tin on tail -03.5

-\$ = 30 μ" (0.76 μm) Gold on contact area, Matte Tin on tail = 3.5 mm-06.5= 6.5 mm (ADM6 only)

-STL = 30 μ" (0.76 μm) Gold on contact area, Tin/Lead on solder tail (ADM6 –01.5 lead style & ADF6 –03.5 lead style only)

-A = Alignment Pin

= Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks)



ADM6

Board Mates: ADF6

Standoffs: JSO, GPSO



-07.5= 7.5 mm (ADF6 only)

-08.5

= 8.5 mm

(ADM6 only)

	((0.70) 028
A	<u> </u>	<u>*</u>

LEAD STYLE	A	В
-01.5	(2.90) .114	(3.32) .131
-03.5	(4.90) .193	(5.32) .209
-06.5	(7.90) .311	(8.32) .328
-08.5	(9.90) .390	(10.32) .406

View complete specifications at: samtec.com?ADM6

MATED HEIGHTS *					
ADF6	ADM6 LEAD STYLE				
LEAD STYLE	-01.5	-03.5	-06.5	-08.5	
-03.5	(5 mm) .197"	(7 mm) .276"	(10 mm) .394"	(12 mm) .472"	
-07.5	(9 mm) .354"	(11 mm) .433"	(14 mm) .551"	(16 mm) .630"	

* Processing conditions will affect mated height.

ADF6

Board Mates: ADM6

Standoffs: JSO, GPSO



	No. of Positions x (0.635) .025 + (4.72) .186 ————————————————————————————————————
Â	\$ AB

LEAD STYLE	A	В
-03.5	(3.23) .127	(3.65) .144
-07.5	(7.23) .285	(7.65) .301

Notes:

Some sizes, styles and options are non-standard, non-returnable

View complete specifications at: samtec.com?ADF6