

ACCLI**MATE**



IP68 SEALED USB & ETHERNET PLUGS

Mates with: SCRES

SPECIFICATIONS

For complete specifications see www.samtec.com?SCPE

Insulator Material: Polycarbonate Contact Material: Phosphor Bronze Shield Material: Phosphor Bronze Wire:


24 AWG
Overmold:
PA66 GF13 FR
Current Rating:
3.8 A per pin (1 pin powered)
Operating Temp Range:
-40 °C to +70 °C
ROHS Compliant:

DUST CAP

• DCA-17-02

Note:

Some lengths, styles and options are non-standard non-returnable.



FIELD TERMINATION KIT

- Ethernet Field Termination Kit available for long cable run and small-opening applications so housings can be customer-installed after the runs are complete.
- SCPFE-17-G-01 Series (For cable outside diameter range of 5.00-5.75 mm)
- SCPFE-17-G-02 Series (For cable outside diameter range of 5.75-6.50 mm)

ALSO AVAILABLE (MOQ REQUIRED)

 Other wire lengths

Mates with: SCRUS

SPECIFICATIONS

For complete specifications see www.samtec.com?SCPU


Insulator Material: Glass Filled Thermoplastic Contact Material: Copper Alloy Shield Material: CRS

Wire:
20 AWG (Power)
25 AWG (Signal)
28 AWG (Drain)
Sealed Overmold:
PA66 GF13 FR
Operating Temp Range:
-20 °C to +75 °C

-20 °C to +75 °C RoHS Compliant: Yes

Note:

Some lengths, styles and options are non-standard, non-returnable.



■ WWW.SAMTEC.COM I