


(0.50 mm) .0197" PITCH • SLH/TLH SERIES

.185



OPTION

-K

(3.00 mm)

.118" DIA

Polyimide

Film

Pick &

Place Pad

SLH Mates: TLH

TLH Mates:

SPECIFICATIONS

Insulator Material: Black Liquid Crystal Polymer Contact Material: Copper Alloy **Plating:** Au over 50 µ" (1.27 µm) Ni **Current Rating:** 2.1 A per pin (2 pins powered) Operating Temp Range: -55 °C to +125 °C

PROCESSING


Lead-Free Solderable:

SMT Lead Coplanarity: (0.10 mm).004**Board Stacking:**

For applications requiring two or more connectors per board, contact ipg@samtec.com



^{*}Processing conditions will affect mated height









"X"R

(Leave blank

for tape &

reel)

-FR

= Full Reel

Tape & Reel


(must order max. quantity per reel;

. contact

Samtec for

quantity

breaks)



Note:

Some lengths, styles and options are non-standard, non-returnable.