

* =NOT RELEASED FOR PRODUCTION .015 0.38 REF $\langle \mathbb{C} \rangle$ SECTION "A"-"A"




		TABLE 4			
LEAD STYLE	BODY	CONTACT	"A"	"B"	"C"
-01	SFM-XX-D-EM-01	C-61-06-X	.126 [3.20]	.031 [0.79]	.082 [2.08]
*-02	SFM-XX-D-EM-02	C-61-08-X	.105 [2.67]	.062 [1.57]	.100 [2.54]
* - NOT BELEASED FOR PRODUCTION					

= NOT RELEASED FOR PRODUCTION

UNLESS OTHERWISE SPECIFIE
DIMENSIONS ARE IN INCHES.

TOLERANCES ARE: DECIMALS ANGLES .XX: ±.01[0.3]

2 ° .XXX: ±.005[0.13] .XXXX: ±.0020[0.051]

PROPRIETARY NOTE THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC,

AREA, MATTE TIN ON TAIL -SM: 30µ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL.

> INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC INC

DO NOT SCALE DRAWING SHEET SCALE: 4:1

INSULATOR: LCP, UL 94 VO, COLOR BLACK

TERMINAL: BeCu, 1/2 HARD, AGE HARDENED

F:\DWG\MISC\MKTG\EMF-1XX-XX-XX-D-MKT.SLDDRW



520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322

.050 X .050 EDGE MOUNT SOCKET STRIP DUAL ROW ASSEMBLY

DWG. NO.

EMF-1XX-XX-XX-D

BY: PURVIS

7-26-96

SHEET 1 OF 1

3. ALL POSITIONS TO BE PACKAGED IN TUBES.

2. MINIMUM PUSHOUT FORCE: .5 LB

NOTES:

PACKAGING VIEW