

OPTION
-N: NON-FLUSH
(SEE NOTE 6)
(NOT AVAILABLE ON LEAD STYLES
-5A, -7, -21A, -21C, & -29)

OPTION
-L: LOCKING LEAD
(ONLY AVAILABLE WITH LEAD STYLES -2 & -22)
(ONLY AVAILABLE WITH -T PLATING)

<u>LEAD STYLE</u> (SEE SOCKET SPECIFICATION, TABLES 1 & 2)

PLATING SPECIFICATION
-G: 30µ" GOLD ON CONTACT,
10µ" GOLD ON SHELL
(SPECIFIY 'GG' IN SOCKET SUFFIX 'XX')
-T: 30µ" GOLD ON CONTACT,

MATTE TIN ON SHELL (-GT OPTION NOT AVAILABLE ON LEAD STYLE -7)

(SPECIFY 'GT' IN SOCKET SUFFIX 'XX')
-TT: MATTE TIN ON CONTACT,

MATTE TIN ON SHELL
(NOT AVAILABLE ON LEAD STYLES)

(NOT AVAILABLE ON LEAD STYLES -7 AND -21 A THRU -39) (SPECIFY 'TT' IN SOCKET SUFFIX 'XX')

 -S: 10µ" SELECTIVE GOLD ON CONTACT, MATTE TIN ON SHELL (ONLY AVAILABLE ON LEAD STYLES -2 & -22)

NOT AVAILABLE ON SDL-) (FOR LOCKING LEAD OPTION, USE SC-1L1-GT)

(SPECIFY 'ST' IN SOCKET SUFFIX 'XX')




FIG 2 SD-1XX-XX-2-N SHOWN (SEE NOTE 6) (SAME AS FIG 1, DIFFERENT AS SHOWN)

FIG 1

SD-1XX-XX-2 SHOWN

NOTES:

1. © REPRESENTS A CRITICAL DIMENSION.

2. MAXIMUM CUT FLASH: .005[0.13] IN ALL AREAS EXCEPT BAR BREAK OFF AREA; .012[0.31] IN BAR BREAK OFF AREA

3. MINIMUM PUSHOUT FORCE: 5 LB

4. MAXIMUM ALLOWABLE BOW: SD: 2-10 POS: .006", 11-19 POS: .008" IN/IN,

20-36 POS: .018" IN/IN; SDL: 2-10 POS: .006",11-19 POS: .015" IN/IN, 20-36 POS: .030" IN/IN.

5. FOR A ONE POSITION SDL, CUT SL-132 TO 2 POSITIONS.

6. FOR -SD WITH -N OPTION, INSERT PIN ON SIDE WITH SMALLER HOLE,

OPPOSITE COUNTERBORE.

7. OPERATOR MUST VERIFY CORRECT PIN BY CHECKING THE NUMBER OF CLIPS.

8. PLATING OPTION -GT NOT AVAILABLE.
9. PLATING OPTION -GG NOT AVAILABLE.

10. POSTIONS 1 - 4 AND ANY BODY/LEAD STYLES NOT LISTED IN THE TUBE TABLE TO BE PACKAGED IN BULK.

	TABLE 1 - SD LEAD STYLES								
LEAD STYLE	SOCKET	"A" (-N OPTION ONLY)		"B" (PIN LENGTH)	No OF FINGER CLIPS				
		MIN	MAX	1` ′	(SEE NOTE 7)				
-1A	SC-1W1-XX-2	N/A	.038 [0.97]	.563 [14.30]	4				
-1B	SC-1W1-XX-1	N/A	.038 [0.97]	.703 [17.86]	4				
-1C	SC-1W1-XX-3	N/A	.038 [0.97]	.453 [11.51]	4				
-2	SC-1P1-XX	.025 [0.64]	.038 [0.97]	.300 [7.62]	4				
*-5A	SC-2P1-XX	N/A	N/A	.703 [17.86]	4				
-7	SC-1P3-XX	.025 [0.64]	.038 [0.97]	.600 [15.24]	4				
-18	SC-6P1-XX	.025 [0.64]	.038 [0.97]	.353 [8.97]	4				
-21A	EZ-1W1-XX-2	N/A	N/A	.553 [14.05]	6				
-21B	EZ-1W1-XX-1	N/A	N/A	.703 [17.86]	6				
-21C	EZ-1W1-XX-3	N/A	N/A	.453 [11.51]	6				
-22	EZ-1P1-XX	.025 [0.64]	.038 [0.97]	.300 [7.62]	6				
-29	EZ-2P2-XX	N/A	N/A	.703 [17.86]	6				
-38	EZ-6P1-XX	.025 [0.64]	.038 [0.97]	.353 [8.97]	6				

* = AVAILABLE TO EXISTING CUSTOMERS ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES. TOLERANCES ARE:

DECIMALS ANGLES
.XX: ±.01 [0.3] 2°
.XXX: ±.005 [0.13]
.XXXX: ±.0020 [0.051]

SOCKET

(SEE TABLE 1)

THIS DOCUMENT CONTAINS CONFIDENTIAL AND
PROPRIETARY INFORMATION AND ALL DESIGN,
MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS
AND SALES RIGHTS ARE EXPRESSY RESERVED BY SAMMED,
INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE
OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR
REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY
OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS
WRITTEN CONSENT OF SAMMET.

PROPRIETARY NOTE

DO NOT SCALE DRAWING SHEET SCALE: 3:1

(SEE TABLE 1 & NOTE 7)

INSULATOR: LCP or NYLON COLOR: BLACK SOCKET: BeCu/BRASS BRASS

F:\DWG\MISC\MKTG\SDX-1XX-XX-XX-X-MKT.SLDDRW



520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322


DESCRIPTION:

SOCKET STRIP ASSEMBLY

DWG. NO.

SDX-1XX-XX-XX-X

BY: J. BROWNING 07/27/2015 SHEET 1 OF 2








TABLE 2 - SDL LEAD STYLES								
LEAD STYLE	SOCKET	"C"		"D" (PIN LENGTH)	No OF FINGER CLIPS (SEE NOTE 7)			
		MIN	MAX		(022 11012 7)			
-10	SC-3P1-XX	.025 [0.64]	.038 [0.97]	.230 [5.84]	4			
-11	SC-4P1-XX	.015 [0.38]	.028 [0.71]	.240 [6.10]	4			
-12	SC-5P1-XX	.015 [0.38]	.028 [0.71]	.190 [4.83]	4			
-19	SC-8P1-XX	.005 [0.13]	.016 [0.41]	.165 [4.19]	4			
-30	EZ-3P1-XX	.025 [0.64]	.038 [0.97]	.230 [5.84]	6			
-31	EZ-4P1-XX	.015 [0.38]	.028 [0.71]	.240 [6.10]	6			
-32	EZ-5P1-XX	.015 [0.38]	.028 [0.71]	.190 [4.83]	6			
-39	EZ-8P1-XX	.005 [0.13]	.016 [0.41]	.165 [4.19]	6			





SHORTER PARTS FIT BETTER AS SHOWN

FOR SDL OPTION

TABLE 3 - PACKAGING TUBES							
BODY STYLE	LEAD STYLE	TUBE	PLUG				
-SD	-1C, -2, -2-L, -18, -21C, -22, -22-L, -38	PT-1-24-01-14	TP-03				
-05	-1A, -21A, -7	PT-1-24-06-03	TP-07				
	-29	PT-1-24-16-29	TP-03				
-SDL	ALL	PT-1-24-01-14	TP-03				

PACKAGING VIEWS
(SEE NOTE 10 & TABLE 3)

THIS DOCUMENT OF PROPRIETARY INFORM MANUFACTURING, RE AND SALES RIGHTS RIGHTS AND SALES RIGHTS AND SALES RIGHTS AND SALES RIGHTS AND SA

PROPRIETARY NOTE

**THIS DOCUMENT CONTAINS CONFIDENTIAL AND
PROPRIETARY INFORMATION AND ALL DESIGN,
MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS
AND SALES RIGHTS ARE EXPRESS IN SERVED BY SAMITEC,
INC. THIS DOCUMENT SHALL NOT RE DISCLOSED, IN WHOLE
OR PART, TO ANY UNAUTH-ORIZED PERSON OR ENTITY MOR
REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY
OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS
WRITTEN CONSENT OF SAMITEC, IN

520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047

PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail info@SAMTEC.com code 55322

DESCRIPTION:

DO NOT SCALE DRAWING

SOCKET STRIP ASSEMBLY

SHEET SCALE: 3:1

SDX-1XX-XX-XX-X

BY: J. BROWNING 07/27/2015 SHEET 2 OF 2

DWG. NO.