


## **REVISION R**

DO NOT SCALE FROM THIS PRINT

## **DESIGNED & DIMENSIONED** IN INCHES [MILLIMETERS]







## NOTES:

- 1. © REPRESENTS A CRITICAL DIMENSION. 2. MINIMUM PUSHOUT FORCE 1.0 LB (4.44N) 3. MAXIMUM BREAKOFF VESTIGE: .015[0.38].

UNLESS OTHERWISE SPECIFIED. DIMENSIONS ARE IN INCHES. TOLERANCES ARE:

INSULATOR: PBT, UL 94V-0 COLOR: SEE COLOR SPECIFICATION

DECIMALS ANGLES .XX: ±.01 [0.3] .XXX: ±.005 [0.13] .XXXX: ±.0020 [0.051]

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN MANUFACTURING REPRODUCTION USE PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

PROPRIETARY NOTE

SHEET SCALE: 8:1 DESCRIPTION

e-Mail info@SAMTEC.com code 55322

520 PARK EAST BLVD, NEW ALBANY, IN 47150

PHONE: 812-944-6733

.100 [2.54] C.L. SHUNT ASSEMBLY

DWG. NO.

SNT-100-XX-X-X

FAX: 812-948-5047


CONTACT: COPPER ALLOY F:\DWG\MISC\MKTG\SNT-100-XX-X-X-MKT.SLDDRW


DO NOT SCALE DRAWING

BY: KOLB

1/31/90

SHEET 1 OF 2





\*-H OPTION (SAME AS FIG 1 EXCEPT AS SHOWN) SNT-100-XX-X-H SHOWN \*= ONLY AVAILABLE WITH -BK OPTION

## \* PROPRIETARY NOTE THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN,

PROPRIETARY INFORMATION AND ALL DESIGN.

MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS

AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMITEC,

INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE

OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR

REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY

OTHER PROJECT IN ANY MANINER THOUT THE EXPRESS

WRITTEN CONSENT OF SAMITEC, INC.



SHEET SCALE: 6:1

DESCRIPTION:

.100 [2.54] C.L. SHUNT ASSEMBLY

DWG. NO.

SNT-100-XX-X-X

BY: KOLB

1/31/90

SHEET 2 OF 2