LOW PROFILE AND ELEVATED ONE-PIECE

(1.00 mm) .0394" PITCH • FSI SERIES

SPECIFICATIONS

Insulator Material: Liquid Crystal Polymer Contact Material: BeCu Current Rating: 2.8 A per pin (2 pins powered) Operating Temp Range: °C to +125 °C

Plating: Au over 50 μ" (1.27 μm) Ni

PROCESSING

Lead-Free Solderable:

Yes SMT Lead Coplanarity: (0.10 mm) .004" max (05-30) (0.15 mm) .006" max (50)* *(.004" stencil solution may be available; contact ipg@samtec.com)

Compression Board: Gold Pads required





10, 20, 30, 50 (Insert/Screw Option)

> 05, 10, 20, 30, 50 (Short Version)

PLATING BODY **HEIGHT OPTION**

-G = 10 µ" (0.25 µm) Gold (-03 only)

on tail

with -03 body

height)

-10 = 10 µ" (0.25 µm) $= 10 \, \text{mm}$

-03

= 3 mm

-06

= 6 mm

ROW **OPTION**

-S Single Row (Available with 5, 10 & 20 pins with –AD alignment pin)

Gold on -D contact, Matte Tin = Double Row (Not available

OPTION

Leave blank for Short Version (No screw down inserts or holes)

= #2-56 x 1/16" screw thread

> -M = 2.00 mm $x 0.40 \, mm$ screw thread

ALIGNMENT **OPTION**

Leave blank for no Alignment Pin

-AD = Alignment Pin Top & Bottom

& -10 body height only) -K

OTHER

OPTION

-WT

(Available with –S row

option & -06

Weld Tab

= Polyimide Film Pick & Place Pad (50 position with threaded insert option only)


-P

= Plastic Pick & Place Pad (5.08 mm) .200" x (12.45 mm) .490" (50 not available with -E) (Not available with -S row option or –03 body height)

> -TR = Tape & Reel

-FR = Full Reel


Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks)


















ALSO AVAILABLE MOQ Required

No alignment pin Top side alignment pin Bottom side alignment pin Other platings

Applications requiring 40-50 positions without threaded inserts, please contact Samtec Interconnect Processing Group.


Some lengths, styles and options are non-standard, non-returnable.











(-06 & -10 Body only)

	BODY HEIGHT	A	В
	-03	(3.00) .118	(8.76) .345
	-06	(6.00) .236	(9.02) .355
	-10	(10.00) .394	(9.02) .355



Insert Option (10, 20 & 30 pins/row)

Single Row Version -03, -06, -10