

BOARD-TO-BOARD GUIDE POST STANDOFF

GPSOM SERIES



GPSOM

Use With: NVAX, ADX6, UMPX, SEAX, ERX8

SPECIFICATIONS

Material: Stainless Steel with black oxide finished

GPSOM

BOARD STACK HEIGHT

Specify BOARD STACK HEIGHT from chart

LEAD STYLE

-01 = Press-In with Nut

MATERIAL


-01 = 303 Stainless Steel with MIL-C-13924 black oxide finish

KIT OPTION

Leave blank for kit

-N

= No hardware (Standoff only)





BOARD STACK HEIGHT	A	В	с
-0700	(7.00) .276	(8.20) .323	(7.00) .276
-0900	(9.00) .354	(10.20) .402	(9.00) .354

GPSOM-XXXX-01-01 SHOWN

(4.76) .187

Notes:

Standoffs to be used with (1.57 mm) .062" min thick boards. Threaded options PCB max thickness of (3.00 mm) .118".

Some sizes, styles and options are non-standard, non-returnable.

Components are to be packaged in separate bags unassembled. Top and bottom components available for purchase separately, contact Samtec.