


ISOLATED POWER SYSTEMS

FEATURES & BENEFITS

- Individually shrouded contacts for electrical and mechanical protection
- .100" (2.54 mm) and .165" (4.19 mm) pitch
- Surface mount or through-hole
- Vertical and right-angle for parallel, perpendicular and coplanar applications
- Locking clip, key polarization and guide post options
- Discrete wire assemblies with 16-30 AWG PVC or Teflon™ fluoropolymer wire (see pages 243-245).
- Metal or plastic rugged latching system

*Teflon $^{™}$ is a trademark of The Chemours Company FC, LLC used under license by Samtec



Selectively loading contacts achieves customer specific creepage and clearance requrements.



Flexible standard or high-power stacking systems with Power Eye three-finger BeCu contacts for reliable connection. For available series, visit samtec.com/flexiblestrips

CREEPAGE & CLEARANCE

| | CREEPAGE | CLEARANCE | |
|------------------------------|----------|-----------|--|
| IPT1/IPS1 MMSS(T)/MMSD(T) | 2.54 mm | 1.91 mm | |
| IPBT/IPBS PMSS(T)/PMSD(T) | 4.27 mm | 3.05 mm | |

Selectively loading contacts achieves customer specific creepage and clearance requirements.

KEY SPECIFICATIONS


| SERIES | PITCH | INSULATOR MATERIAL | CONTACT MATERIAL | PLATING | OPERATING TEMP RANGE | CURRENT RATING | VOLTAGE RATING | LEAD-FREE SOLDERABLE |
|-----------|--------------------|-----------------------|--|---|-------------------------|---------------------------|-------------------|-------------------------|
| IPT1/IPS1 | .100" (2.54 mm) | Black LCP | Phosphor Bronze | Sn or Au over 50 µ" (1.27 µm) Nickel | -55 °C to +125 °C | 5.9 A (1 pin powerd) | 775 VAC | Yes |
| IPBT/IPBS | .165" (4.19 mm) | Black LCP | High Copper Alloy (IPBT) Phospher Bronze (IPBS) | Sn over 50 μ" (1.27 μm) Nickel | -55 °C to +105 °C | 10.3 A (2 pins powerd) | 400 VAC | Yes |







(2.54 mm) .100" PITCH • SHROUDED POWER CONNECTOR SET



Board Mates:

PINS

IPT1/IPS1

CURRENT RATING (PER CONTACT)

5.9 A 4.8 A




| TO TOTAL AV | |
|-------------|----------|
| | (5 .2 |

| No. of positions x (2.54) .100 + (0.51) .020 | → |
|---|----------|
| (5.08) | |
| Through-hole Surface Mou | nt |



(7.16) - .282




-VS

-RA

| -rk |
|--|
| = Full Reel Tape & Reel |
| (must order max. quantity |
| per reel; contact Samtec |
| per reel; contact Samtec for quantity breaks) |
| (-VS only) |
| |

| LEAD STYLE | MATED HEIGHT | A | В |
|---------------|-----------------|----------------|-------------|
| -01 | (11.05) .435 | (6.35) .250 | (2.16) .085 |
| -01-VS | (13.59) .535 | (6.35) .250 | N/A |
| -02 | (14.00) .551 | (9.30) .366 | (2.64) .104 |
| -03 | (16.00) .630 | (11.30) .445 | (2.16) .085 |
| -04 | (17.00) .669 | (12.30) .484 | (2.69) .106 |
| -05 | (19.00) .748 | (14.30) .563 | (2.46) .097 |
| -06 | (20.00) .787 | (15.30) .602 | (2.35) .093 |
| -07 | (25.00) .984 | (20.30) .799 | (2.31) .091 |
| -08 | (30.00) 1.181 | (25.30) .996 | (2.39) .094 |
| -09 | (35.00) 1.378 | (30, 30) 1 193 | (2 46) 097 |



Note:

Some lengths, styles and non-returnable.

View complete specifications at: samtec.com?IPT1 & samtec.com?IPS1