

PSS-08-01-T-S PSS-13-01-T-S **PSS SERIES** 

(5.08 mm) .200"

# **POWER SOCKET STRIP**

## **SPECIFICATIONS**

For complete specifications and recommended PCB layouts see www.samtec.com?PSS

Insulator Material: Black LCP

Contact Material:

Plating:

Sn over 50 μ" (1.27 μm) Ni Current Rating (PSS/FWS):

11.4 A per pin

(1 pin powered)
Insertion Depth:
(2.62 mm) .103" to
(5.03 mm) .198"

Voltage Rating: 500 VAC mated with FWS

**RoHS Compliant:** Yes

### **PROCESSING**

Lead-Free Solderable:

Yes SMT Lead Coplanarity: (0.15 mm) .006" max (02-14)\* (0.20 mm) .008" max (15-20)\* \*(.004" stencil solution


may be available; contact ipg@samtec.com)


### **RECOGNITIONS**

For complete scope of recognitions see www.samtec.com/quality



Mates with: FWS, HFWS, SW, HPM, HPW





Some lengths, styles and options are non-standard, non-returnable.