








SPM, MUSBS SERIES

IP68 SEALED MINI USB PORT



SPECIFICATIONS


For complete specifications and recommended PCB layouts see www.samtec.com?MUSBS

Insulator Material:

Black High Temperature
Thermoplastic
Contact Material:
Phosphor Bronze
Shell Material:
Phosphor Bronze
Plating:
Gold on Mating Area,
Nickel on Shell, Tin on Tails
Operating Temp Range:
-50°C to +85°C
Current Rating:
2A per contact
Voltage Rating: 30 VRMS
Contact Resistance:

 $50~\text{m}\Omega$ max Minimum Cycles: 5000 RoHS Compliant:

Lead-Free Solderable:



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM