


50 Ω TNC TO 6 GHz



-P

= PCB

Mount


Cable Mates: RF174, RF178, RF316, RS316, RF058, GRF1H-C





_J

= Jack



-H

= 30 µ" (0.76 µm) Gold

center contact, Nickel on shell

TNC **Cable Connectors** TNC-CA



Supplied with pins, washers, nuts and ferrules. See website for dimensions.

SR = Straight Reverse Polarity

CONNECTORS FOR INDUSTRY STANDARD CABLES	
TNC-P-C-GN-ST-CA1	RG 174/316 Cable
TNC-P-C-GN-ST-CA2	RG 178 Cable
TNC-P-C-GN-SR-C10	RG 58 Cable
TNC-J-C-GN-ST-BH1	RG 174/316 Cable, Bulkhead
TNC-J-C-GN-ST-BH2	RG 178 Cable, Bulkhead
P-C = Cable Plug J-C = Cable Jack GN = Plating (10 μ" Gold on contact, Nickel on body) ST = Straight	

(29.80) 1.173 -J 25.00)

-P

-RA

= Right-angle

-TH1

= Through-hole

samtec.com/TNC