



VSWR - MICROWAVE / MILLIMETER WAVE CABLE ASSEMBLIES

HIGH-FREQUENCY CABLE ASSEMBLIES FROM 18 GHz TO 65 GHz

- Samtec offers a wide range of low loss microwave / millimeter wave cable assemblies
- Cable types include .047, .085, .086, .178, .277 and Samtec optimized varieties
- In addition to VSWR numbers, test plots, complete characterization reports, and engineering prints are also available at samtec.com/RF



	Interface Type	VSWR
RF086	1.85 mm	1.40 max
	2.40 mm	1.40 max
	2.92 mm	1.40 max
	SMMP	1.40 max
RF047-A	1.85 mm	1.40 max
	2.40 mm	1.35 max
	2.92 mm	1.35 max
	SMMP	1.40 max
RF085	2.40 mm	1.40 max
	2.92 mm	1.40 max
RF23S	3.50 mm	1.30 max
RF25S	SMP	Contact Samtec
	SMA	1.60 max
RF405	SMP	Contact Samtec
	SMA	1.35 max
RF402	SMA	1.50 max
RF180	SMA	1.35 max
	TNCA	1.35 max
	N Type	1.35 max
RF280	SMA	1.35 max
	TNCA	1.35 max
	N Type	1.35 max
RF120	2.40 mm	1.40 max
	2.92 mm	1.40 max
RF23C	2.40 mm	1.40 max
	2.92 mm	1.40 max
	SMMP	1.40 max

For more information about Samtec's RF cable assemblies, please contact: RFGroup@samtec.com