



# SEALED I/O SYSTEMS



# SEALED I/O ACCLIMATE™ SYSTEMS

IP67 & IP68 • BAYONET/PUSH-PULL CIRCULARS • SPACE-SAVING RECTANGULARS




## ACCLIMATE™

### FLEXIBLE SEALED CIRCULAR SYSTEMS

- Metal or plastic, 12 mm, 16 mm and 22 mm shells
- Flexible pin configuration, gender and panel interface termination
- Bayonet-style latching systems meet IP68 requirements
- Cost-effective crimp version available
- Mini push-pull latching system meets IP67 requirements for dust and waterproof sealing




Kitted components for efficient field assembly



## SEALED RECTANGULARS

- Space saving design
- Meets IP68 requirements
- USB and Ethernet signal systems
- Rugged dust caps available
- 1 or 2-port vertical and right-angle panel mount sockets



## THREADED CIRCULARS

- Meets IP68 requirements for dust and waterproof sealing
- Rugged overmold design
- USB and Ethernet signal systems
- 17 shell size
- Rugged dust caps and panel-to-board termination available



**samtec**  
SUDDEN SERVICE®

UNITED STATES • NORTHERN CALIFORNIA • SOUTHERN CALIFORNIA • SOUTH AMERICA • UNITED KINGDOM  
GERMANY • FRANCE • ITALY • NORDIC/BALTIC • BENELUX • ISRAEL • INDIA • AUSTRALIA / NEW ZEALAND  
SINGAPORE • JAPAN • CHINA • TAIWAN • HONG KONG • KOREA

**[samtec.com/sealed](http://samtec.com/sealed)**