



30 AWG POWER CABLE HT

DWCT-30-01




PERFORMANCE DATA

Flex Cycles:	5,000 cycles*
Current Rating:	Single = 2.3 Amps**
Voltage Rating:	300 V***
CC DCR:	101 Ω/1000 ft
Availability:	Single, tape bonded
Temperature Rating:	-10 °C to 200 °C, UL VW-1 Rated*** -40 °C to 200 °C****
DWV Working Voltage:	1250 V†

* Test Conditions – 2 oz. weight, dia 1/4" mandrel, +/-90 bend X2
 ** Rating – 30 °C Temperature Rise, 20% de-rated.
 *** Test Conditions - UL certification under style #10518, horizontal and
 VW-1 flame rating
 **** Test Conditions – Heat Shock/Cold Bend per UL #1581,
 wire wrap 1/4" mandrel, visual inspection
 † Test Conditions – DWV per EIA-364-20, ASTM D470-13 and D149-09

CURRENT CARRYING CAPACITY GRAPH**



1.800.SAMTEC.9 • HDR@samtec.com