

REVISION N

RECOMMENDED PCB LAYOUT FOR MEC1-1XX-XX-XX-D-RAX-XX-SL-XX





F:\DWG\MISC\Mktg\Footprnt\MEC1-1XX-XX-X-D-RAX-X-SL-FOOTPRINT.SLDDRW

TABLE 3								
# POSITIONS	"D"	"E"						
-05	N/A	N/A						
-08	.039 [1.00]	N/A						
-20	.236 [6.00]	N/A						
-30	.354 [9.00]	N/A						
-40	.551 [14.00]	N/A						
-50	.748 [19.00]	N/A						
-60	.551 [14.00]	1.181 [30.00]						
-70	.984 [25.00]	2.205 [56.00]						

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES. TOLERANCES ARE:

DECIMALS ANGLES
.XX: ±.010[0.25] 2 °
.XXX: ±.005[0.13]
.XXXX: ±.0020[0.051]

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMPTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ARY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTER CONSENS OF SAMPTEC.



520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322

REVISION N

RECOMMENDED STENCIL LAYOUT FOR MEC1-1XX-XX-XX-D-RAX-XX-SL-XX

NOTE: STENCIL TO BE .0060[.152] THICK.







FIG 2 MEC1-160-XX-XX-D-RAX-SL STENCIL LAYOUT SHOWN







* PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND

THIS DOCUMENT INFORMATION AND ALL DESIGN,
MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS
AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC,
INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE
OR PART, TO ANY UNAUTHORIZED PERSON OR ENTRO
REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY
OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS
WRITTER CORSENT OF SAMTEC.



REVISION N RECOMMENDED MATING CARD LAYOUT FOR MEC1-1XX-XX-XX-D-RAX-XX-SL-XX


TABLE 1										
POSITION	"A" (CARD SLOT 1)		"B" (CARD SLOT 2)		"F"		"G"			
-05	.094	[2.39]		N/A	0.266	[6.75]	0.1576	[4.003]		
-08	.133	[3.38]	N/A		0.384	[9.75]	0.2758	[7.005]		
-20	.330	[8.38]	N/A		0.857	[21.76]	0.7486	[19.014]		
-30	.448	[11.38]	N/A		1.251	[31.77]	1.1426	[29.022]		
-40	.645	[16.38]	N/A		1.645	[41.78]	1.5366	[39.030]		
-50	.842	[21.39]	N/A		2.039	[51.79]	1.9306	[49.037]		
-60	.645	[16.38]	1.275	[32.37]	2.433	[61.79]	2.3246	[59.045]		
-70	1.078	[27.38]	2.298	[58.37]	2.827	[71.80]	2.7186	[69.052]		

NOTES:

- 1. -60 AND -70 ARE THE ONLY TWO CARDS THAT HAVE TWO SLOTS.
- 2. MIRROR IMAGE FOOTPRINT ON THE OTHER SIDE OF PCB.
 3. FOR NON-POLARIZED OPTION, REPLACE SLOTS WITH TRACES.
 4. ALL DIMENSIONS ARE SYMMETRIC ABOUT CENTERLINE.
- 5. PLATING TO BE .000030 INCHES GOLD WITH HARDNESS
- 130-200 KNOOP PER ASTM B488 TYPE 2, GRADE C.
- 6. POSITIONS -05, -08, -20 & -30 ARE POLARIZED UNLESS OTHERWISE NOTED WITH OPTION -NP.
- 7. FOR PROPER CONTACT REGISTRATION, PLATING BUS TIES TO BE WIDTH
- OF THE EDGE FINGER.

 N 8. FOR APPLICATIONS REQUIRING INVERTED REFLOW SOLDERING, USE OF AN EPOXY ADHESIVE IS RECOMMENDED.

 $\frac{\hbox{FIG 3}}{\hbox{MEC1-160-02-X-D-RAX-XX-SL}} \ \hbox{MATING CARD SHOWN}$



OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY

520 PARK EAST BLVD, NEW ALBANY, IN 47150

FAX: 812-948-5047

-Sheet 3 of 3^{\perp}

PHONE: 812-944-6733