


DO NOT
SCALE FROM
THIS PRINT






RECOMMENDED PANEL CUTOUT

DESIGNED & DIMENSIONED
IN INCHES[MILLIMETERS]

PRF01-J-C-EP-170A-BS

SERIES
-01: SMA
GENDER
-J: JACK
TYPE
-C: CABLE
TERMINATION
-S: SOLDER CLAMP
ORIENTATION
-B: BULKHEAD
CABLE TYPE
-170A: STORM VSR190
FINISH
-EP: 50μ" EXTRA HEAVY GOLD
CENTER CONTACT, PASSIVATED
OUTER CONTACT



EXPLODED VIEW
NOT TO SCALE
(FOR CLARITY ONLY)

- NOTES:
1. MATERIAL:
BODY, LOCK WASHER, LOCK NUT & CLAMP NUT: STAINLESS STEEL.
SOCKET: BERYLLIUM COPPER.
SOLDER FERRULE: BRASS.
O-RING: SILICONE RUBBER.
INSULATOR: PTFE.
DIELECTRIC BEADS: ULTEM 1000.
 2. FINISH:
BODY, LOCK WASHER, LOCK NUT & CLAMP NUT: PASSIVATED.
SOCKET & SOLDER FERRULE: GOLD OVER NICKEL PLATE,
50 μIN MIN GOLD OVER 50 μIN MIN NICKEL.
 3. PCI P/N: 3225.

UNLESS OTHERWISE SPECIFIED,
DIMENSIONS ARE IN INCHES.
TOLERANCES ARE:
DECIMALS ANGLES
.XX: ±.01 [0.3]
.XXX: ±.005 [0.13]
.XXXX: ±.0005 [0.013]

* PROPRIETARY NOTE *

THIS DOCUMENT CONTAINS CONFIDENTIAL AND
PROPRIETARY INFORMATION AND ALL DESIGN,
MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS
AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC,
INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE
OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR
REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY
OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS
WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING SHEET SCALE: 1.5:1

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail info@SAMTEC.com code 55322

DESCRIPTION: SMA BULKHEAD JACK FOR STORM
VSR190 CABLE

DWG. NO. PRF01-J-C-EP-170A-BS

BY: SAMUEL C 08/07/2020 SHEET 1 OF 1