

DO NOT SCALE FROM THIS PRINT

SMA STYLE

- *-1.85: 1.85mm SMAS
- *-2.40: 2.40mm SMAS
- *-2.92: 2.92mm SMAS

BOARD TO BOARD HEIGHT

- *-005: 5.0mm
- *-007: 7.0mm
- *-009: 9.0mm
- *-010: 10mm
- *-011: 11mm
- *-012: 12mm
- *-014: 14mm
- *-16M: 16mm USING 3.5mm ADF6
- *-16F: 16mm USING 7.5mm ADF6
- *-020: 20mm


* = NOT TOOLED

TABLE A

SMA STYLE	STACK HEIGHT	PART NUMBER
*1.85	005	S-REF-212056-1.85-005
	*007	S-REF-212056-1.85-007
	*009	S-REF-212056-1.85-009
	*010	S-REF-212056-1.85-010
	*011	S-REF-212056-1.85-011
	*012	S-REF-212056-1.85-012
	*014	S-REF-212056-1.85-014
	*16M	S-REF-212056-1.85-16M
*16F	S-REF-212056-1.85-16F	
*020	S-REF-212056-1.85-020	
2.40	005	S-REF-212056-2.40-005
	*007	S-REF-212056-2.40-007
	*009	S-REF-212056-2.40-009
	*010	S-REF-212056-2.40-010
	*011	S-REF-212056-2.40-011
	*012	S-REF-212056-2.40-012
	*014	S-REF-212056-2.40-014
	*16M	S-REF-212056-2.40-16M
*16F	S-REF-212056-2.40-16F	
*020	S-REF-212056-2.40-020	
2.92	005	S-REF-212056-2.92-005
	*007	S-REF-212056-2.92-007
	*009	S-REF-212056-2.92-009
	*010	S-REF-212056-2.92-010
	*011	S-REF-212056-2.92-011
	*012	S-REF-212056-2.92-012
	*014	S-REF-212056-2.92-014
	*16M	S-REF-212056-2.92-16M
*16F	S-REF-212056-2.92-16F	
*020	S-REF-212056-2.92-020	

* = NOT TOOLED

NOTES:
1. ESD BAGS NOT SHOWN FOR CLARITY



BOM TABLE

ITEM	PART NUMBER	DESCRIPTION	COST	QTY	QTY
1	SEE TABLE A	EVALUATION KIT		1	1
2	FP-FMC004	BOX		1	1
3	S-FMC010	SLEEVE		1	1
4	F-FMC005	FOAM		1	1
5	CCS-207056-01-MC	FLASH DRIVE		1	1
6	LABEL-MAIL-1IN-CLR	LABEL		2	2

SIGNAL MAPPING

ADF6	REF DES	J8	J9	J13	J14	J10	J11	J15	J16	J5	J6	J20	J21	J3	J4	J18	J19
	CONNECTOR PIN	B13	B14	C15	C16	B17	B18	C19	C20	A19	A20	D17	D18	A15	A16	D13	D14
ADM6	REF DES	J8	J9	J13	J14	J10	J11	J15	J16	J5	J6	J20	J21	J3	J4	J18	J19
	CONNECTOR PIN	B13	B14	C15	C16	B17	B18	C19	C20	A19	A20	D17	D18	A15	A16	D13	D14

TOLERANCES DO NOT APPLY TO REFERENCE DIMENSIONS. UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES. TOLERANCES ARE:
DECIMALS .XX: ±.01 | .3
.XXX: ±.005 | .13
.XXXX: ±.0020 | .051

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING SHEET SCALE: 1:4

MATERIAL:

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail info@SAMTEC.com code 53322

DESCRIPTION: ADX6 EVALUATION PLATFORM

DWG. NO. REF-212056-X.XX-XXX

BY: JAMES BA. 8/29/2019 SHEET 1 OF 1