

SEAFC TO SEAC MATED VIEWS

DESIGNED & DIMENSIONED
IN MILLIMETERS [INCHES]




FIGURE 1
SEAFC MATED WITH SEAC

TABLE 1

		SEAFC LEAD STYLE								WIPE			
		-05.0		-06.0		-06.5		-07.5					
		"A" FULLY MATED	"A" MAX	"A" FULLY MATED	"A" MAX	"A" FULLY MATED	"A" MAX	"A" FULLY MATED	"A" MAX				
SEAC LEAD STYLE	W/T Latch	.934 [23.72]	.950 [24.13]	.973 [24.72]	.989 [25.13]	.993 [25.22]	1.009 [25.63]	1.032 [26.22]	1.048 [26.63]	.043 [1.09]	.027 [0.69]		
	W/O Latch	.819 [20.80]	.847 [21.51]	.858 [21.80]	.886 [22.51]	.878 [22.30]	.906 [23.01]	.917 [23.30]	.945 [24.01]	.043 [1.09]	.015 [0.38]		

NOTES:

1. ALL DIMENSIONS BASED ON NOMINAL VALUES FOR SAMTEC RECOMMENDED PCB LAYOUTS.
2. ALTHOUGH MAX DIMENSIONS ARE LISTED SAMTEC RECOMMENDS FULLY MATING COMPONENTS.