


DESIGNED & DIMENSIONED  
IN MILLIMETERS[INCHES]

TABLE 1

No. OF POS	"A"	"B"	"C"	"D"
-02	9.10 [0.358]	3.50 [0.138]	1.00 [0.039]	6.50 [0.256]
-03	10.10 [0.398]	4.50 [0.177]	2.00 [0.079]	7.50 [0.295]
-04	11.10 [0.437]	5.50 [0.217]	3.00 [0.118]	8.50 [0.335]
-05	12.10 [0.476]	6.50 [0.256]	4.00 [0.157]	9.50 [0.374]
-06	13.10 [0.516]	7.50 [0.295]	5.00 [0.197]	10.50 [0.413]
-07	14.10 [0.555]	8.50 [0.335]	6.00 [0.236]	11.50 [0.453]
-08	15.10 [0.594]	9.50 [0.374]	7.00 [0.276]	12.50 [0.492]
-09	16.10 [0.634]	10.50 [0.413]	8.00 [0.315]	13.50 [0.531]
-10	17.10 [0.673]	11.50 [0.453]	9.00 [0.354]	14.50 [0.571]
-11	18.10 [0.713]	12.50 [0.492]	10.00 [0.394]	15.50 [0.610]
-12	19.10 [0.752]	13.50 [0.531]	11.00 [0.433]	16.50 [0.650]
-13	20.10 [0.791]	14.50 [0.571]	12.00 [0.472]	17.50 [0.689]
-14	21.10 [0.831]	15.50 [0.610]	13.00 [0.512]	18.50 [0.728]
-15	22.10 [0.870]	16.50 [0.650]	14.00 [0.551]	19.50 [0.768]
-16	23.10 [0.909]	17.50 [0.689]	15.00 [0.591]	20.50 [0.807]
-17	24.10 [0.949]	18.50 [0.728]	16.00 [0.630]	21.50 [0.846]
-18	25.10 [0.988]	19.50 [0.768]	17.00 [0.669]	22.50 [0.886]
-19	26.10 [1.028]	20.50 [0.807]	18.00 [0.709]	23.50 [0.925]
-20	27.10 [1.067]	21.50 [0.846]	19.00 [0.748]	24.50 [0.965]

B

FIG.1  
(-10 POSITION SHOWN)  
(T1M-XX-XX-DV-X PCB LAYOUT SHOWN)

## NOTES:

1. ALL DIMENSIONS ARE SYMMETRIC ABOUT THE CENTERLINE, EXCEPT AS SHOWN.
2. CONNECTOR ENVELOPE DIMENSIONS, OTHER COMPONENTS PLACED ON PCB SHALL AVOID THIS ZONE.

\* PROPRIETARY NOTE \*

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

**Samtec**

520 PARK EAST BLVD, NEW ALBANY, IN 47150  
PHONE: 812-944-6733 FAX: 812-948-5047  
e-Mail: info@SAMTEC.com code 55322

NOTE:  
STENCIL TO BE 0.13[.005] THICK.




FIG 2  
(-10 POSITION SHOWN)  
(T1M-XX-XX-DV-X STENCIL SHOWN)