RECOMMENDED PCB LAYOUT FOR TMMH-1XX-XX-DV-XXX-XXX-FOOTPRINT **REVISION B**

1/13/2012 ECN-169918





FIG 1 TMMH-112-XX-XX-DV-XXX-XXX (-A / -LC OPTIONS) В

TABLE 1		
OPTIONS	"A"	"B"
NONE	.038 [0.97]	N/A
-A	.045 [1.14]	.047 [1.19]
-LC	.045 [1.14]	.047 [1.19]

PROPRIETARY NOTE THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTEC, INC. AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE OTHER THAN THAT WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC, INC.





REVISION B RECOMMENDED STENCIL LAYOUT FOR TMMH-1XX-XX-DV-XXX-XXX-FOOTPRINT SAME AS FIG 1 UNLESS NOTED OTHERWISE RECOMMENDED STENCIL THICKNESS .006[.152]

PROPRIETARY NOTE THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTEC, INC. AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHER DOCUMENTS OR DUSCLOSED TO OTHERS OR USED FOR ANY PURPOSE OTHER THAN THAN WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC, INC.



PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322 SHEET 3 OF 3