


NOTES:

1. Ⓞ REPRESENTS A CRITICAL DIMENSION.
2. BURR ALLOWANCE: 0.038[.0015] MAX.
3. ROHS COMPLIANT.
4. PARTS TO BE PACKAGED IN TRAY.





DO NOT SCALE FROM THIS PRINT

**DESIGNED & DIMENSIONED
IN MILLIMETERS[INCHES]**



USBR-A-S-X-O-VU

- TYPE
-A
- ROW SPECIFICATION
-S: SINGLE
- OPTION
-VU: UPRIGHT ENTRY
- COLOR
-O: ORANGE
- PLATING SPECIFICATION
-F: 1 μ" FLASH GOLD ON CONTACT AREA, MATTE TIN ON TAIL
-S: 30 μ" SELECTIVE GOLD ON CONTACT AREA, MATTE TIN ON TAIL



UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS[INCHES]. TOLERANCES ARE: DECIMALS ANGLES X.X: ±0.25[.01] X.XX: ± 0.13[.005] X.XXX: ± 0.05[.002]	PROPRIETARY NOTE THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTEC, INC. AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE OTHER THAN THAT WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC, INC.		520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 fromparent+PHONE: 812-944-6733 FAX: 812-948-5047
			MATERIAL: DO NOT SCALE DRAWING SHEET SCALE: 3:1 INSULATOR: PA 9T. COLOR: ORANGE CONTACT : PHOSPHOR BRONZE C5191H SHELL: BRASS C2680H
		DWG. NO. USBR-A-S-X-O-VU	
		BY: VICKY Z 05/19/2009 SHEET 1 OF 1	