

# CABLE CONNECTORS, PRECISION RF



## INDUSTRY STANDARD CABLE COMPATIBILITY GUIDE

Series	GHz	Type	Industry Cable
PRF10	110	1.00 mm	.047, semi-rigid
PRF18	65	1.85 mm	.047, semi-rigid
			.047 Temp-Flex, low loss flexible, 29 AWG
			Harbour SS405, flexible alternative to RG 405
			RG 405, .085, semi-rigid
			.086 Temp-Flex, low loss flexible
PRFM0	65	SMPM	.047 Temp-Flex, low loss flexible, 29 AWG
			.047 Temp-Flex, low loss flexible, 28 AWG
			Harbour SS405, flexible alternative to RG 405
PRF24	50	2.40 mm	.086 Temp-Flex, low loss flexible
			Harbour SS405, flexible alternative to RG 405
			RG 405, .085, semi-rigid
			.086 Temp-Flex, low loss flexible
			Semflex HP120, low loss flexible
			Semflex HP160, low loss flexible
			IW 1401, low loss flexible
			IW 1501, low loss flexible
Dynawave DF150, low loss flexible			
PRF92	40	2.92 mm	.047, semi-rigid
			RG 405, .085, semi-rigid
			.085, semi-rigid, 23 AWG
			Harbour SS405, flexible alternative to RG 405
			.086 Temp-Flex, low loss flexible
			Haverhill HC35004, .118, semi-rigid
			Semflex HP120, low loss flexible
			RG 402, .141, semi-rigid
			Semflex HP160, low loss flexible
			IW 1501, low loss flexible
			Dynawave DF150, low loss flexible
			Dynawave DF140, low loss flexible
			Harbour LL142, low loss flexible
			Semflex HP190, low loss flexible
			Times Max Gain 200, low loss flexible
PRF00	40	SMP	.047 Temp-Flex, low loss flexible, 29 AWG
			.085, semi-rigid, 23 AWG

Series	GHz	Type	Industry Cable			
PRF35	34	3.50 mm	RG 405, .085, semi-rigid			
			Semflex HP120, low loss flexible			
			RG 402, .141, semi-rigid			
			Semflex HP160, low loss flexible			
PRFS1	34	SSMA	RG 405, .085, semi-rigid			
			Harbour SS402, flexible alternative to RG 402			
PRF01	18	SMA	.047, semi-rigid			
			RG 405, .085, semi-rigid			
			Harbour LL120, low loss flexible			
			IW 1201, low loss flexible			
			RG 402, .141, semi-rigid			
			Semflex HP160, low loss flexible			
			Dynawave DF150, low loss flexible			
			Harbour SS402, flexible alternative to RG 402			
			Harbour LL142, low loss flexible			
			Harbour SB142, low loss flexible			
			Semflex HP190, low loss flexible			
			Times Max Gain 200, low loss flexible			
			Semflex LA290, low loss flexible			
			Harbour LL335i, low loss flexible			
			Harbour LL335, low loss flexible			
			Semflex HP305, low loss flexible			
			PRF06	18	N Type	Harbour LL142, low loss flexible
						Harbour SB142, low loss flexible
Semflex HP190, low loss flexible						
Semflex LA290, low loss flexible						
Harbour LL335i, low loss flexible						
Harbour LL335, low loss flexible						
PRF04	18	TNCA	Semflex HP305, low loss flexible			
			Semflex HP120, low loss flexible			
			Harbour SS402, flexible alternative to RG 402			
			RG 402, .141, semi-rigid			
			Harbour LL142, low loss flexible			
			Semflex HP190, low loss flexible			
			Semflex LA290, low loss flexible			
			Harbour LL335i, low loss flexible			
			Harbour LL335, low loss flexible			

