



Cross Reference of EIA-364 Procedures and MIL-STD-1344 Methods

TEST	EIA-364 Procedure	MIL-STD-1344 Method
Mating and unmating forces	EIA-364-13	MIL-STD-1344 Method 2013
Temperature life with or without electrical load	EIA-364-17	MIL-STD-1344 Method 1005
Withstanding voltage	EIA-364-20	MIL-STD-1344 Method 3001
Insulation resistance	EIA-364-21	MIL-STD-1344 Method 3003
Low level contact resistance	EIA-364-23	MIL-STD-1344 Method 3002
Salt spray	EIA-364-26	MIL-STD-1344 Method 1001
Mechanical shock (specified pulse)	EIA-364-27	MIL-STD-1344 Method 2004
Vibration	EIA-364-28	MIL-STD-1344 Method 2005
Humidity	EIA-364-31	MIL-STD-1344 Method 1002
Thermal shock (temperature cycling)	EIA-364-32	MIL-STD-1344 Method 1003
Contact engagement and separation force	EIA-364-37	MIL-STD-1344 Method 2014