

Series: QFS-DP/QMS-DP

Description: Micro High Speed Board-to-Board, 0.635mm Pitch, 14mm (0.5512") Stack Height

Frequency Domain Data Summary

Table 1 - Differential Connector System Performance		
Test Parameter	Configuration	
Insertion Loss	SS	3dB@ 6.45 GHz
Return Loss	SS	>10dB to 4.8 GHz
Near-End Crosstalk	AAQQ	<-20dB to 20.0 GHz
	Xrow, AA to QQ	<-20dB to 20.0 GHz
Far-End Crosstalk	AAQQ	<-20dB to 20.0 GHz
	Xrow, AA to QQ	<-20dB to 20.0 GHz

Bandwidth Chart – Differential Insertion Loss

QFS-DP/QMS-DP Connector Series

