

Series: QTE-DP/QSE-DP**Description:** High-Speed Board-to-Board, 0.8mm (.0315") Pitch, 16mm (.630") Stack Height**Frequency Domain Data Summary**

Table 1 - Differential Connector System Performance		
Test Parameter	Configuration	
Insertion Loss	GSSG	3dB @ 9.075 GHz
Return Loss	GSSG	>10dB to 3.675 GHz
Near-End Crosstalk	GAAQQG	< -20dB to 20.000 GHz
	GAAGQQG	< -20dB to 20.000 GHz
	Xrow, GAAG to GQQG	< -20dB to 20.000 GHz
Far-End Crosstalk	GAAQQG	< -20dB to 20.000 GHz
	GAAGQQG	< -20dB to 20.000 GHz
	Xrow, GAAG to GQQG	< -20dB to 20.000 GHz

Series: QTE-DP/QSE-DP

Description: High-Speed Board-to-Board, 0.8mm (.0315") Pitch, 16mm (.630") Stack Height

Bandwidth Chart – Differential Insertion Loss

QTE/QSE Differential Ground Plane Header Series

