

Series: MIT-DP/MIS-DP, Mixed Technology

Description: Parallel Board-to-Board, 0.635mm Pitch, 22mm (0.866") Stack Height

Frequency Domain Data Summary

Table 1 - Differential Connector System Bandwidth		
Test Parameter	Configuration	
Insertion Loss	SS	-3dB @ 8.18 GHz
Return Loss	SS	< -5dB to 8.18 GHz
Near-End Crosstalk	AA QQ	< -22dB to 8.18 GHz
	Xrow, AA to QQ	< -38dB to 8.18 GHz
Far-End Crosstalk	AA QQ	< -28dB to 8.18 GHz
	Xrow, AA to QQ	< -40dB to 8.18 GHz

**PCB/Connector Test System
Differential Application
MIS-01 / MIT-06 DP version**

