

Series: QFS-DP/QMS-DP, Micro High Speed

Description: Parallel Board-to-Board, 0.635mm Pitch, 11mm (0.433") Stack Height

Frequency Domain Data Summary

Table 1 - Differential Connector System Bandwidth		
Test Parameter	Configuration	
Insertion Loss	SS	-3dB @ 6.70 GHz
Return Loss	SS	< -5dB to 6.70 GHz
Near-End Crosstalk	AA QQ	< -22dB to 6.70 GHz
	Xrow, AA to QQ	< -30dB to 6.70 GHz
Far-End Crosstalk	AA QQ	< -25dB to 6.70 GHz
	Xrow, GAAG to GQQG	< -28dB to 6.70 GHz

**PCB/Connector Test System
Differential Application
QFS-01-DP / QMS-11-DP**

