

FIG. 1
PCB LAYOUT FOR MPTC-XX-XX-XX-6.30-XX-X-V-LC SHOWN




FIG. 2
PCB LAYOUT FOR MPTC-XX-XX-00-6.30-XX-X-V-LC SHOWN

- NOTES:
1. CONNECTOR ENVELOPE DIMENSIONS. OTHER COMPONENTS PLACED ON PCB SHALL AVOID THIS ZONE.
 2. ALL DIMENSIONS ARE SYMMETRIC ABOUT THE CENTERLINE.
 3. EACH GROUP HOLDS ONE POWER PIN.
 4. NOTE DELETED.
 5. ONLY REQUIRED ON MPTC-02-XX-02-6.30-XX-X-V-XX

**DESIGNED & DIMENSIONED
IN MILLIMETERS [INCHES]**

F:\dwg\misc\mktg\footprnt\MPTC-XX-XX-XX-6.30-XX-X-V-XX-FOOTPRINT.SLDDRW

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

samtec
520 PARK EAST BLVD., NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail info@SAMTEC.com code 55322

TABLE 1

PART NUMBER	"A"	"B"	"C"	"D"
MPTC-01-04-01-X.XX-XX-X-V-XX	21.44 [0.844]	16.51 [0.650]	10.77 [0.424]	N/A
MPTC-02-04-02-X.XX-XX-X-V-XX	31.44 [1.238]	26.51 [1.044]	20.77 [0.818]	N/A
MPTC-01-08-01-X.XX-XX-X-V-XX	23.44 [0.923]	18.51 [0.729]	12.77 [0.503]	2.00 [0.079]
MPTC-02-08-02-X.XX-XX-X-V-XX	33.44 [1.317]	28.51 [1.122]	22.77 [0.896]	2.00 [0.079]
MPTC-01-16-01-X.XX-XX-X-V-XX	27.44 [1.080]	22.51 [0.886]	16.77 [0.660]	6.00 [0.236]
MPTC-02-16-02-X.XX-XX-X-V-XX	37.44 [1.474]	32.51 [1.280]	26.77 [1.054]	6.00 [0.236]
MPTC-01-24-01-X.XX-XX-X-V-XX	31.44 [1.238]	26.52 [1.044]	20.79 [0.818]	10.00 [0.394]
MPTC-02-24-02-X.XX-XX-X-V-XX	41.44 [1.631]	36.52 [1.438]	30.79 [1.211]	10.00 [0.394]
MPTC-01-36-01-X.XX-XX-X-V-XX	37.44 [1.474]	32.51 [1.280]	26.77 [1.054]	16.00 [0.630]
MPTC-02-36-02-X.XX-XX-X-V-XX	47.44 [1.868]	42.51 [1.674]	36.77 [1.448]	16.00 [0.630]
MPTC-01-40-01-X.XX-XX-X-V-XX	39.44 [1.868]	34.51 [1.359]	28.77 [1.448]	18.00 [0.709]
MPTC-02-40-02-X.XX-XX-X-V-XX	49.44 [1.868]	44.51 [1.752]	38.77 [1.448]	18.00 [0.709]
MPTC-01-48-01-X.XX-XX-X-V-XX	43.44 [1.710]	38.51 [1.516]	32.77 [1.290]	22.00 [0.866]
MPTC-02-48-02-X.XX-XX-X-V-XX	53.44 [2.104]	48.51 [1.910]	42.77 [1.684]	22.00 [0.866]
MPTC-01-80-01-X.XX-XX-X-V-XX	59.44 [2.340]	54.51 [2.146]	48.77 [1.920]	38.00 [1.496]
MPTC-02-80-02-X.XX-XX-X-V-XX	69.44 [2.734]	64.51 [2.540]	58.77 [2.314]	38.00 [1.496]
MPTC-03-12-00-X.XX-XX-X-V-XX	31.44 [1.238]	26.51 [1.044]	NA	4.00 [0.157]
MPTC-04-12-00-X.XX-XX-X-V-XX	36.44 [1.435]	31.51 [1.241]	NA	4.00 [0.157]
MPTC-03-16-00-X.XX-XX-X-V-XX	33.44 [1.317]	28.51 [1.122]	NA	6.00 [0.236]
MPTC-04-16-00-X.XX-XX-X-V-XX	38.44 [1.513]	33.51 [1.319]	NA	6.00 [0.236]
MPTC-03-20-00-X.XX-XX-X-V-XX	35.44 [1.395]	30.51 [1.201]	NA	8.00 [0.315]
MPTC-04-20-00-X.XX-XX-X-V-XX	40.44 [1.592]	35.51 [1.398]	NA	8.00 [0.315]
MPTC-03-24-00-X.XX-XX-X-V-XX	37.44 [1.474]	32.51 [1.280]	NA	10.00 [0.394]
MPTC-04-24-00-X.XX-XX-X-V-XX	42.44 [1.671]	37.51 [1.477]	NA	10.00 [0.394]

M

* PROPRIETARY NOTE *

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.



520 PARK EAST BLVD, NEW ALBANY, IN 47150
 PHONE: 812-944-6733 FAX: 812-948-5047
 e-Mail info@SAMTEC.com code 55322