


DESIGNED AND DIMENSIONED IN INCHES[MILLIMETERS]
ALL DIMENSIONS REFERENCE EXCEPT AS SHOWN

185-J-P-EG-ST-AL-01-X

DO NOT
SCALE FROM
THIS PRINT



GENDER
-J: JACK

TYPE
-P: PCB






FINISH
-EG: 50μ" EXTRA HEAVY GOLD
CENTER CONTACT, 10μ" GOLD
OUTER CONTACT

PACKAGING
-BLANK: INDIVIDUALLY BAGGED
-B: FULL TRAY (QTY = X00)

OPTION
-01: PCB THICKNESS .0040" TO 0.100"

TERMINATION
-AL: ANGLED LAUNCH, 30 DEGREE
COMPRESSION MOUNT

ORIENTATION
-ST: STRAIGHT



NOTES:

1. RECOMMENDED TORQUE 0.5~0.8 INCH-POUNDS.
2. THIS IS A GENERAL FOOTPRINT AND IS NOT OPTIMIZED FOR ELECTRICAL PERFORMANCE, CONTACT SIG@SAMTEC.COM FOR ASSISTANCE WITH ELECTRICAL LAYOUT.

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS CONFIDENTIAL AND PROPRIETARY INFORMATION AND ALL DESIGN, MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

MATERIAL: DO NOT SCALE DRAWING SHEET SCALE: 6:1
BODY, BUSHING & SCREW: STAINLESS STEEL
SOCKET: BeCu COPPER ALLOY
MOUNTING HARDWARE: STAINLESS STEEL

DESCRIPTION: 1.85MM JACK 30 DEG ANGLED LAUNCH

DWG. NO. 185-J-P-EG-ST-AL-01-X

BY: MATT M 8/2/2024 SHEET 1 OF 1

samtec

520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322