

No. OF POS	"A"	"B"
-10	.450 [11.43]	.696 [17.68]
-20	.950 [24.13]	1.196 [30.38]
-30	1.450 [36.83]	1.696 [43.08]
-40	1.950 [49.53]	2.196 [55.78]
-50	2.450 [62.23]	2.696 [68.48]

No. OF ROWS	"C"	"D"	"G"
-04	.150 [3.81]	.278 [7.06]	.063 [1.60]
-06	.250 [6.35]	.378 [9.60]	.035 [0.89]
-08	.350 [8.89]	.478 [12.14]	.035 [0.89]
-10	.450 [11.43]	.578 [14.68]	.035 [0.89]

	Ni uin (um)		Au uin (um)		Sn uin (um)	
	ENIG	HASL/Immersion	2 - 8	(0.05 - 0.20)	NA	NA
	100 - 200	NA	(2.50 - 5.00)	NA	100 - 800	NA
	NA	NA	NA	NA	(2.50 - 20.00)	NA

NOTES:

1. ALL DIMENSIONS ARE SYMMETRIC ABOUT THE CENTERLINE.
2. CONNECTOR ENVELOPE DIMENSIONS, OTHER COMPONENTS PLACED ON PCB SHALL AVOID THIS ZONE.
3. RECOMMENDED SILKSCREEN FOR PROPER CONNECTOR ORIENTATION TO PCB.
4. CONTACT SAMTEC FOR CONNECTOR PRESS FIT INSTRUCTIONS AND REQUIRED FIXTURES.
5. FOR TERMINATION INSTRUCTIONS CONTACT SAMTEC IPG

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTEC, INC. AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE OTHER THAN THAT WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC, INC.



520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322




FIG 2
(GUIDE POST OPTION)
(SEAMP-20-02.0-X-06-GP1 FOOTPRINT SHOWN)
(SAME AS FIG 1 EXCEPT AS SHOWN)

TABLE 3

No. OF POS	"E"	"F"
-10	1.033 [26.24]	1.266 [32.16]
-20	1.533 [38.94]	1.766 [44.86]
-30	2.033 [51.64]	2.266 [57.56]
-40	2.533 [64.34]	2.766 [70.26]
-50	3.033 [77.04]	3.266 [82.96]

ALL DIMENSIONS ARE SYMMETRIC ABOUT THE CENTERLINE.

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC, INC. AND SHALL NOT BE REPRODUCED
OR TRANSFERRED TO OTHER DOCUMENTS OR
DISCLOSED TO OTHERS OR USED FOR ANY
PURPOSE OTHER THAN THAT WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED WRITTEN
CONSENT OF SAMTEC, INC.



520 PARK EAST BLVD, NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322