





XQXX-XXX-XXXX-SBR-TBL-X-X

ALL DIMENSIONS REF
DO NOT SCALE
FROM THIS PRINT

| SERIES | "D" | "K" |
|--------|---------------|---------------|
| EQCD | 0.501 [12.73] | 0.775 [19.69] |
| SQCD | 0.625 [15.88] | 0.775 [19.69] |
| HQCD | 0.751 [19.08] | 0.775 [19.69] |
| EQDP | 0.525 [13.34] | 0.775 [19.69] |
| HQDP | 0.800 [20.32] | 0.875 [22.23] |
| EQSD | 0.780 [19.30] | 0.775 [19.69] |



ONLY APPLICABLE FOR SCREW-DOWN END OPTIONS



| EQCD | SQCD | HQCD | EQDP | HQDP | EQSD | "E" | "F" |
|------------------|------------------|------------------|------------------|------------------|------------------|----------------|----------------|
| No. OF POSITIONS | No. OF POSITIONS | No. OF POSITIONS | No. OF POSITIONS | No. OF POSITIONS | No. OF POSITIONS | | |
| N/A | N/A | N/A | N/A | N/A | -020 | 1.439 [36.55] | 1.665 [42.39] |
| N/A | N/A | N/A | N/A | N/A | -040 | 2.227 [56.55] | 2.456 [62.39] |
| -020 | -025 | -030 | -014 | N/A | N/A | 1.339 [34.00] | 1.679 [40.10] |
| -040 | -050 | -060 | -028 | N/A | N/A | 2.126 [54.00] | 2.386 [60.10] |
| -060 | -075 | -090 | -042 | N/A | N/A | 2.913 [74.00] | 3.154 [80.10] |
| -080 | -100 | -120 | -056 | N/A | N/A | 3.701 [94.00] | 3.941 [100.10] |
| N/A | N/A | N/A | N/A | -020 | N/A | 1.489 [37.82] | 1.719 [43.85] |
| N/A | N/A | N/A | N/A | -040 | N/A | 2.414 [61.32] | 2.644 [67.16] |
| N/A | N/A | N/A | N/A | -060 | N/A | 3.339 [84.81] | 3.569 [90.65] |
| N/A | N/A | N/A | N/A | -080 | N/A | 4.264 [108.31] | 4.494 [114.15] |

| EQCD | SQCD | HQCD | EQDP | HQDP | EQSD | "A" | "B" | "J" |
|------------------|------------------|------------------|------------------|------------------|------------------|----------------|---------------|---------------|
| No. OF POSITIONS | No. OF POSITIONS | No. OF POSITIONS | No. OF POSITIONS | No. OF POSITIONS | No. OF POSITIONS | | | |
| N/A | N/A | N/A | N/A | N/A | -020 | 1.275 [32.39] | 1.178 [29.92] | 0.950 [24.13] |
| N/A | N/A | N/A | N/A | N/A | -040 | 2.063 [52.39] | 1.965 [49.92] | 0.950 [24.13] |
| -020 | -025 | -030 | -014 | N/A | N/A | 1.175 [29.85] | 1.078 [27.38] | 0.950 [24.13] |
| -040 | -050 | -060 | -028 | N/A | N/A | 1.963 [49.85] | 1.866 [47.40] | 0.950 [24.13] |
| -060 | -075 | -090 | -042 | N/A | N/A | 2.750 [69.85] | 2.653 [67.39] | 0.950 [24.13] |
| -080 | -100 | -120 | -056 | N/A | N/A | 3.538 [89.85] | 3.441 [87.39] | 0.950 [24.13] |
| N/A | N/A | N/A | N/A | -020 | N/A | 1.325 [33.66] | 1.128 [28.65] | 1.150 [29.21] |
| N/A | N/A | N/A | N/A | -040 | N/A | 2.250 [57.15] | 2.053 [52.13] | 1.150 [29.21] |
| N/A | N/A | N/A | N/A | -060 | N/A | 3.175 [80.65] | 2.978 [75.64] | 1.150 [29.21] |
| N/A | N/A | N/A | N/A | -080 | N/A | 4.100 [104.14] | 3.903 [99.12] | 1.150 [29.21] |

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTEC, INC. AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE OTHER THAN THAT WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC, INC.



520 PARK EAST BLVD. NEW ALBANY, IN 47150
PHONE: 812-944-6733 FAX: 812-948-5047
e-Mail: info@SAMTEC.com code: 55322

SHEET SCALE: 1.25:1
F:\DWG\WISC\ymktg\XQXX\XQXX-SBR-TBL.sldrw

DESCRIPTION:
QXS / QTX CABLE ASSEMBLY
DWG. NO.
XQXX-XXX-XXXX-SBR-TBL-X-X
BY: BRATCHER 6/26/2003 SHEET 1 OF 1