# ACCELERATE® SLIM, DIRECT ATTACH CABLE ASSEMBLIES

(0.635 mm) .025" PITCH



# PAM4

# **FEATURES & BENEFITS**

- Slimmest cable assembly in the industry 7.6 mm width
- High-density 2-row design
- 8, 16 and 24 differential pair configurations
- 34 AWG, 100  $\Omega$  Eye Speed\* ultra low skew twinax cable
- Multiple wiring options including reverse polarity
- Mating board level socket (ARF6 Series) features standard rugged weld tabs for increased stability on the PCB
- Rugged metal latching and shielding
- Supports 64 Gbps PAM4 (32 Gbps NRZ) applications
- PCIe<sup>®</sup> 6.0/CXL<sup>™</sup> 3.1 capable
- Utilizes Samtec's Flyover® Technology to simplify board layout and extend signal reach



Right-angle available. Visit samtec.com?ARF6-RA for specifications.



Contacts directly soldered to the twinax for improved signal integrity

## KEY SPECIFICATIONS (ARC6/ARF6)

РІТСН	CABLE	SIGNAL ROUTING	INSULATOR MATERIAL	CONTACT MATERIAL	PLATING	OPERATING TEMP RANGE
(0.635 mm) .025"	34 AWG Eye Speed® ultra low skew twinax	100 $\Omega$ Differential	Black LCP	Copper Alloy	Au over 50 μ" (1.27 μm) Ni	-40 °C to +125 °C

PCI-SIG®, PCI Express® and the PCIe® design marks are registered trademarks and/or service marks of PCI-SIG.

F-224 (Rev 19DEC23)


#### samtec.com/AcceleRate-Cable

Unless otherwise approved in writing by Samtec, all parts and components are designed and built according to Samtec's specifications which are subject to change without notice.





### (0.635 mm) .025" • SLIM CABLE & SOCKET



#### samtec.com/AcceleRate-Cable

Unless otherwise approved in writing by Samtec, all parts and components are designed and built according to Samtec's specifications which are subject to change without notice.