ACCLIMATE

IP68 SEALED ETHERNET SOCKET

RPBE, RPCE SERIES



RPBE

Mates with:

SPECIFICATIONS

Insulator Material: Black Liquid Crystal Polymer

Contact: Phosphor Bronze

Operating Temp Range: -40 °C to +75 °C Seal: Rubber Screw:

Stainless Steel Sealing Washer:

Stainless Steel Nut:

Rubber

RPBE


NO. OF PORTS


-01, -02

LEAD STYLE

-01 = Right-angle **PLATING**

= 50μ " (1.27 μ m) Gold on contact, Flash Gold on tail





NO. OF PORTS	A	В	С
-01	(46.10)	(36.95)	(19.72)
	1.815	1.455	.776
-02	(67.10)	(57.95)	(40.72)
	2.642	2.281	1.603

DUST CAPS

-01 = DCA-RPBE-01-01-P (Push-On/No Latch)

-01 = DCA-RPBE-01-01-L (Latching)

-02 = DCA-RPBE-02-01-L (Latching)

RPCE Mates with:

RPCE



PLATING

= 50 μ" (1.27 μm) Gold on contact,

CABLE LENGTH

-00.25

= (0.25 m) 9.84"

END OPTION

C₅E

SPECIFICATIONS

Insulator Material: Glass Filled Thermoplastic Contact: Phosphor Bronze

Shield: Phosphor Bronze

Operating Temp Range: $-40 \,^{\circ}\text{C}$ to $+75 \,^{\circ}\text{C}$

Overmold: Rite Flex 640F Seal: Rubber

Screw: Stainless Steel Nut:

Stainless Steel Sealing Washer:

Rubber Wire: 24 AWG (╬

Nickel on shell -00.50= (0.50 m) 19.69"

Standard lengths

-D = Double Ended

-BC

= Blunt Cut

Cable Length + (17.01) .669

Note:

Some lengths, styles and options are non-standard, non-returnable

(46.10) 1.815