

SHROUDED .025" SQ POSTIDC HEADERS

(2.54 mm) .100" PITCH • TST/HTST/ZST SERIES



TST/HTST/ZST

Mates:

IDSD, HCSD

SPECIFICATIONS

Insulator Material:

TST, ZST=Black Glass Filled Polyester HTST=Natural LCP Insulation Resistance: $5000 \text{ M}\Omega$ min

Terminal Material: Phosphor Bronze Plating:

Au or Sn over
50 μ" (1.27 μm) Ni
Operating Temp Range:
-55 °C to +125 °C with Gold
-55 °C to +105 °C with Tin
Voltage Rating:
425 VAC/600 VDC

PROCESSING

Lead-Free Solderable: HTST=Yes TST, ZST= No, Lead Wave only SMT Lead Coplanarity: (0.10 mm) .004" max (05-15) (0.15 mm) .006" max (17-36)*

SERIES

TST

HTST

= High Temp Cable Strip

LEAD STYLE

-01

-02

-03

THROUGH-HOLE

(A)

(2.92) .115

(4.19) .165

(14.35) .565

Cable Strip

1

NO. PINS PER ROW

05, 07, 08, 10, 12, 13, 15, 17, 20, 25, 32, 36 (Standard sizes)

0 0 0 0 0

.

-D

LEAD STYLE

Specify LEAD STYLE from chart

)oooo

.

-D-RA

LEAD

STYLE

Specify

LEAD

STYLE

from

chart

-F = Gold flash on post, Matte Tin on tail (Not available on -DV)

PLATING

OPTION

-L = 10 µ" (0.25 µm) Gold on post, Matte Tin on tail

-T = Matte Tin

(9.27) .365

ROW OPTION

-D Double Row

Through-hole (lead style -01, -02 & -03 only)

= Double Row Surface Mount (lead style -01 only) (HTST only)

-D-RA = Double Row Right-angle (lead style -04 & -05 only)

OTHER OPTION

Surface Mount (lead style –01 only) (HTST only)

-P

= Pick & Place Pad


-TR = Tape & Reel

-FR

= Full Reel Tape & Reel (must order max. quantity per reel; contact Samtec for quantity breaks)

SMT Lead Coplanarity: (0.10 mm) .004" max (05-15) (0.15 mm) .006" max (17-36)* *(.004" stencil solution may be available; contact ipg@samtec.com)

A D



(2.54) .100 x No. of Positions + (7.62) .300

(2.54) .100 x No. of Positions + (5.08) .200 -

0 0 0 0

(- - - -

-DV



D

LEAD STYLE	RIGHT- ANGLE (B)
-04	(3.30) .130
-05	(5.84) .230

BODY HEIGHT

-"XXXX"

= Body Height


ALSO AVAILABLE MOQ Required

Other platings & sizes Alignment Pins Single Row Locking Leads Polarized

ZST - 1 NO. PINS PER ROW

05, 07, 08, 10, 12, 13, 15, 17, 20, 25, 32, 36 (Standard sizes)

(2.54) .100 x No. of Positions + (7.62) .300 — (2.54) .100 x No. of Positions + (5.08) .200 — (9.27)



(2.29) BODY HEIGHT C (OAL)

PLATING OPTION

-F = Gold flash on post, Matte Tin on tail

-L = 10 μ" (0.25 μm) Gold on post, Matte Tin on tail

-T = Matte Tin

LEAD STYLE	C (OAL)	MAX BODY HEIGHT
-01	(16.00) .630	(13.72) .540
-02	(18.54) .730	(16.26) .640
-03	(21.08) .830	(18.80) .740
-04	(23.62) .930	(21.34) .840
-05	(26.16) 1.030	(23.88) .940
-06	(28.70) 1.130	(26.42) 1.040
-07	(31.24) 1.230	(28.96) 1.140
-08	(33.78) 1.330	(31.50) 1.240
-09	(36.32) 1.430	34.04) 1.340

Note:

For added mechanical stability, Samtec recommends mechanical board spacers be used in applications with gold or selective gold plated connectors. Contact ipg@samtec.com for more information.

Note:

Some lengths, styles and options are non-standard, non-returnable. ZST is non-standard, non-returnable.