




EXTREME PERFORMANCE & DENSITY ARRAYS

0.80 mm PITCH NOVARAY™ ULTRA-HIGH SPEED SYSTEM


- 112 Gbps PAM4 per channel
- 4.0 Tbps aggregate data rate - 9 IEEE 400G channels
- Fully shielded differential pair design
- Extremely low crosstalk (to 40 GHz)
- Tight impedance control
- Minimal variance in data rate as stack height increases
- 112 differential pairs per square inch
- Utilizes 40% less space with the same data throughput as compared to traditional arrays
- Stub-free mating
- 92 Ω solution addresses both 85 Ω and 100 Ω applications

NOVARAY™




NRZ	PAM4
56 Gbps	112 Gbps


High-speed mezzanine connector and cable in one product family



BGA attach to board for greater density and optimized trace breakout region



Guaranteed two points of contact ensure a more reliable connection



Aggregate Data Rate (NRZ)					
448 Gbps	672 Gbps	896 Gbps	1344 Gbps	1792 Gbps	4032 Gbps*
1 Bank		2 Bank		3 Bank*	
2 Row	3 Row	4 Row	2 Row	3 Row	4 Row
8 Pairs	12 Pairs	16 Pairs	24 Pairs	32 Pairs	72 Pairs*

* In development

System

- **NVAM** – 0.80 mm Pitch Terminal
- **NVAF** – 0.80 mm Pitch Socket
- **NVAC** – 0.80 mm Pitch Socket Cable Assembly
- **NVAM-C** – 0.80 mm Pitch Terminal for NVAC Series

For more information about NovaRay™, please visit samtec.com/novaray