

YTE-110-02-G-6-500





(2.00 mm) .0787"

YTE SERIES

HIGH-DENSITY ELEVATED SOCKET STRIP

SPECIFICATIONS

For complete specifications see www.samtec.com?YTE

Insulator Material: Black Liquid Crystal Polymer Contact Material: Phosphor Bronze Operating Temp Range: -55 °C to +105 °C


-35 C to +105 C Plating: Sn or Au over 50 μ" (1.27 μm) Ni Insertion Depth: (2.62 mm) .103" to (5.03 mm) .198" with (0.38 mm) .015" wipe Max Cycles: 100 with 10 μ" (0.25 μm) Au RoHS Compliant:


Yes Lead-Free Solderable: Wave only

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality







Note: This Series is non-standard, non-returnable.