



VITA 57.4 FMC+ Extender

Application Note

SEPTEMBER 2019

© Samtec, Inc.

VITA 57.4 FMC+ Extender Card

For VITA 57.4 Applications

Samtec Inc.
520 Park East Boulevard
New Albany, IN 47151-1147
1-800-SAMTEC-9
info@samtec.com

COPYRIGHTS, TRADEMARKS AND PATENTS

Product names used herein are trademarks of their respective owners. All information and material in this publication are property of Samtec, Inc. All related rights are reserved. Samtec, Inc. does not authorize customers to make copies of the content for any use.

Terms of Use

Use of this publication is limited to viewing the pages for evaluation or purchase. No permission is granted to the user to copy, print, distribute, transmit, display in public, or modify the contents of this document in any way.

Disclaimer

The information in this publication may change without notice. All materials published here are “As Is” and without implied or express warranties. Samtec, Inc. does not warrant that this publication will be without error, or that defects will be corrected. Samtec, Inc. makes every effort to present our customers an excellent and useful publication, but we do not warrant or represent the use of the materials here in terms of their accuracy, reliability or otherwise. Therefore, you agree that all access and use of this publication’s content is at your own risk.

Updated Documentation

Please visit www.samtec.com to get access to the latest documentation and to ensure that you have the latest version of this document.

NEITHER SAMTEC, INC. NOR ANY PARTY INVOLVED IN CREATING, PRODUCING, OR DELIVERING THIS PUBLICATION SHALL BE LIABLE FOR ANY DIRECT, INCIDENTAL, CONSEQUENTIAL, INDIRECT, OR PUNITIVE DAMAGES ARISING OUT OF YOUR ACCESS, USE OR INABILITY TO ACCESS OR USE THIS PUBLICATION, OR ANY ERRORS OR OMISSIONS IN ITS CONTENT.

1 Abstract

FPGA carrier card developers require easy-to-use options to confirm the operation of the VITA 57.4 FMC+ expansion connector typically found on these platforms. In some cases, the mating height of the standard FMC+ connectors may prevent fully leveraging the connectivity options of all FMC+ modules.

The VITA 57.4 FMC+ Extender Card (REF-212564-01) has been designed for placement between FPGA Carrier Cards and FMC+ Modules. This increased space can be used for additional I/O expansion during development. The FMC+ Extender Card also provides a cost-effective option for extending the life of the FPGA Carrier Card HSPC connectors used as test platforms. It is ideal for benchtop testing, system debugging, probing, or FPGA development.

The card provides FPGA designers an easy to use option for testing low-speed interfaces and high-speed multi-gigabit transceivers on any FPGA development board or FPGA carrier card. It can run system data or BER testing on all channels in parallel. This makes evaluation and development with an FPGA much easier.

This paper will explore the following details of the FMC+ Extender Card:

- Mechanical Dimensions and Assembly Features
- Connector Pin Assignments and Block Diagrams
- Qualification testing set-up and test results

2 Mechanical Dimensions

The FMC+ Extender Card provides a variant of the mechanical dimensions of an FMC+ card defined within ANSI/VITA 57.4-2019 Section 3. The electromechanical interface between the mating HSPC connectors conforms to ANSI/VITA 57.4-2019 Section 3. Specific mechanical dimensions of the card are highlighted below.




Figure 1 - Mechanical Dimensions for FMC+ Extender Card

3 Mechanical Design Features

Since many of the applications that involve VITA 57.4 systems are on highly populated with sensitive components, it is important to have an easy way to access the FMC+ carrier. The FMC+ Extender Card provides several mechanical features that ease mating and unmating.

The FMC+ Loopback Cards feature:

- The FMC+ Loopback cards have been designed to work in conjunction with the [Micro Jack Screw Standoff \(JSOM\)](#).
- Use JSOMs to carefully mate and unmate the FMC+ Loopback Cards to the FPGA carrier to avoid damages.
- An Allen-key unscrews and expands the jack screw, dividing the PCBs in a steady, even motion until the mezzanine is safely separated from its host.

4 Connector Pin Assignments

The FMC+ Extender Card conforms to the Connector Pin Assignments of the HSPC connector as defined within ANSI/VITA 57.4-2019 Section 5. The FMC+ Extender Card provides direct pass-through connectivity for all 560 pins from the HSPC male to HSPC female connectors. Specific pin assignments are highlighted below.

| 14 x 40 | M | L | K | J | H | G | F | E | D | C | B | A | Z | Y |
|---------|------------|---------------|--------------|--------------|-------------|------------|-----------|-----------|---------------|-----------|---------------|------------|------------------|------------|
| 1 | GND | RES1 | VREF_B_M2C | GND | VREF_A_M2C | GND | PG_M2C | GND | PG_C2M | GND | CLK_DIR | GND | HSPC_PSRNT_M2C_L | GND |
| 2 | DP23_M2C_P | GND | GND | CLK3_BIDIR_P | PRSN1_M2C_L | CLK1_M2C_P | GND | HA01_P_CC | GND | DP0_C2M_P | GND | DP1_M2C_P | GND | DP23_C2M_P |
| 3 | DP23_M2C_N | GND | GND | CLK3_BIDIR_N | GND | CLK1_M2C_N | GND | HA01_N_CC | GND | DP0_C2M_N | GND | DP1_M2C_N | GND | DP23_C2M_N |
| 4 | GND | GBTCLK4_M2C_P | CLK2_BIDIR_P | GND | CLK0_M2C_P | GND | HA00_P_CC | GND | GBTCLK0_M2C_P | GND | DP9_M2C_P | GND | DP22_C2M_P | GND |
| 5 | GND | GBTCLK4_M2C_N | CLK2_BIDIR_N | GND | CLK0_M2C_N | GND | HA00_N_CC | GND | GBTCLK0_M2C_N | GND | DP9_M2C_N | GND | DP22_C2M_N | GND |
| 6 | DP22_M2C_P | GND | GND | HA03_P | GND | LA00_P_CC | GND | HA05_P | GND | DP0_M2C_P | GND | DP2_M2C_P | GND | DP21_C2M_P |
| 7 | DP22_M2C_N | GND | GND | HA03_N | GND | LA00_N_CC | GND | HA05_N | GND | DP0_M2C_N | GND | DP2_M2C_N | GND | DP21_C2M_N |
| 8 | GND | GBTCLK3_M2C_P | HA02_P | GND | LA02_P | GND | HA04_P | GND | LA01_P_CC | GND | DP8_M2C_P | GND | DP20_C2M_P | GND |
| 9 | GND | GBTCLK3_M2C_N | HA02_N | GND | LA02_N | GND | HA04_N | GND | LA01_N_CC | GND | DP8_M2C_N | GND | DP20_C2M_N | GND |
| 10 | DP21_M2C_P | GND | HA06_P | HA07_P | LA04_P | LA03_P | HA08_P | HA09_P | LA06_P | GND | DP3_M2C_P | GND | DP10_M2C_P | GND |
| 11 | DP21_M2C_N | GND | HA06_N | HA07_N | LA04_N | LA03_N | HA08_N | HA09_N | LA06_N | GND | DP3_M2C_N | GND | DP10_M2C_N | GND |
| 12 | GND | GBTCLK2_M2C_P | GND | HA11_P | GND | LA08_P | GND | HA13_P | LA05_P | GND | DP7_M2C_P | GND | DP11_M2C_P | GND |
| 13 | GND | GBTCLK2_M2C_N | GND | HA11_N | GND | LA08_N | GND | HA13_N | LA05_N | GND | DP7_M2C_N | GND | DP11_M2C_N | GND |
| 14 | DP20_M2C_P | GND | HA10_P | GND | LA07_P | GND | HA12_P | GND | LA09_P | LA10_P | GND | DP4_M2C_P | GND | DP12_M2C_P |
| 15 | DP20_M2C_N | GND | HA10_N | GND | LA07_N | GND | HA12_N | GND | LA09_N | LA10_N | GND | DP4_M2C_N | GND | DP12_M2C_N |
| 16 | GND | SYNC_C2M_P | HA17_P_CC | HA14_P | GND | LA12_P | GND | HA16_P | LA09_P | LA10_P | GND | DP6_M2C_P | GND | DP13_M2C_P |
| 17 | GND | SYNC_C2M_N | HA17_N_CC | HA14_N | GND | LA12_N | GND | HA16_N | LA09_N | LA10_N | GND | DP6_M2C_N | GND | DP13_M2C_N |
| 18 | DP14_C2M_P | GND | GND | HA18_P | GND | LA16_P | GND | HA20_P | LA13_P | LA14_P | GND | DP5_M2C_P | GND | DP14_M2C_P |
| 19 | DP14_C2M_N | GND | GND | HA18_N | GND | LA16_N | GND | HA20_N | LA13_N | LA14_N | GND | DP5_M2C_N | GND | DP14_M2C_N |
| 20 | GND | REFCLK_C2M_P | HA21_P | HA15_P | GND | LA19_P | GND | HA19_P | LA17_P_CC | GND | GBTCLK1_M2C_P | GND | GBTCLK5_M2C_P | GND |
| 21 | GND | REFCLK_C2M_N | HA21_N | HA15_N | GND | LA19_N | GND | HA19_N | LA17_N_CC | GND | GBTCLK1_M2C_N | GND | GBTCLK5_M2C_N | GND |
| 22 | DP15_C2M_P | GND | HA23_P | HA22_P | GND | LA20_P | GND | HB02_P | LA18_P_CC | GND | DP1_C2M_P | GND | DP15_M2C_P | GND |
| 23 | DP15_C2M_N | GND | HA23_N | HA22_N | GND | LA20_N | GND | HB02_N | LA18_N_CC | GND | DP1_C2M_N | GND | DP15_M2C_N | GND |
| 24 | GND | REFCLK_M2C_P | GND | HB01_P | GND | LA22_P | GND | HB05_P | LA23_P | GND | DP9_C2M_P | GND | DP10_C2M_P | GND |
| 25 | GND | REFCLK_M2C_N | GND | HB01_N | GND | LA22_N | GND | HB05_N | LA23_N | GND | DP9_C2M_N | GND | DP10_C2M_N | GND |
| 26 | DP16_C2M_P | GND | HB00_N_CC | GND | LA21_P | GND | HB04_P | GND | LA26_P | LA27_P | GND | DP2_C2M_P | GND | DP11_C2M_P |
| 27 | DP16_C2M_N | GND | HB00_N | GND | LA21_N | GND | HB04_N | GND | LA26_N | LA27_N | GND | DP2_C2M_N | GND | DP11_C2M_N |
| 28 | GND | SYNC_M2C_P | HB06_P_CC | HB07_P | LA24_P | LA25_P | HB08_P | HB09_P | GND | GND | DP8_C2M_P | GND | DP12_C2M_P | GND |
| 29 | GND | SYNC_M2C_N | HB06_N_CC | HB07_N | LA24_N | LA25_N | HB08_N | HB09_N | GND | GND | DP8_C2M_N | GND | DP12_C2M_N | GND |
| 30 | DP17_C2M_P | GND | GND | HB11_P | GND | LA29_P | GND | HB13_P | TDI | SCL | GND | DP3_C2M_P | GND | DP13_C2M_P |
| 31 | DP17_C2M_N | GND | GND | HB11_N | GND | LA29_N | GND | HB13_N | TDI | SCL | GND | DP3_C2M_N | GND | DP13_C2M_N |
| 32 | GND | RES2 | HB10_P | HB15_P | GND | LA31_P | GND | HB19_P | GND | DP7_C2M_P | GND | DP16_M2C_P | GND | GND |
| 33 | GND | RES2 | HB10_N | HB15_N | GND | LA31_N | GND | HB19_N | GND | DP7_C2M_N | GND | DP16_M2C_N | GND | GND |
| 34 | DP18_C2M_P | GND | HB14_P | HB15_P | LA30_P | LA31_P | HB16_P | HB19_P | TRST_L | GA0 | GND | DP4_C2M_P | GND | DP17_M2C_P |
| 35 | DP18_C2M_N | GND | HB14_N | HB15_N | LA30_N | LA31_N | HB16_N | HB19_N | TRST_L | GA1 | 12P0V | GND | DP4_C2M_N | DP17_M2C_N |
| 36 | GND | 12P0V | GND | HB18_P | GND | LA33_P | GND | HB21_P | 3P3V | GND | DP6_C2M_P | GND | DP18_M2C_P | GND |
| 37 | GND | 12P0V | GND | HB18_N | GND | LA33_N | GND | HB21_N | 3P3V | GND | DP6_C2M_N | GND | DP18_M2C_N | GND |
| 38 | DP19_C2M_P | GND | HB17_N_CC | GND | LA32_P | GND | HB20_P | GND | 3P3V | GND | GND | DP5_C2M_P | GND | DP19_M2C_P |
| 39 | DP19_C2M_N | GND | HB17_N | GND | LA32_N | GND | HB20_N | GND | 3P3V | GND | GND | DP5_C2M_N | GND | DP19_M2C_N |
| 40 | GND | 12P0V | VIO_B_M2C | GND | VADJ | GND | VADJ | GND | 3P3V | GND | RES0 | GND | 3P3V | GND |


Figure 2 - HSPC Connector Pin Assignments

5 Block Diagrams

The FMC+ Extender Card provides basic throughput functionality for testing general FPGA carrier cards that contain the HSPC interface. Signals routed include:

- Gigabit data signals (MGTS)
- Gigabit reference clocks
- Control lines including JTAG (including IPMI support), I2C, addressing, and reserved signals
- All required power rails, sequencing, and control lines

Specific high-level signal routing for both cards are highlighted below.



NOTE: Block diagram shows pin numbers and not signal names.

Figure 3 - FMC+ Extender Card Block Diagram

Additional signal routing and circuitry details are contained in the schematics for the FMC+ Extender. Schematics are available from Samtec under NDA. Please e-mail KitsAndBoards@samtec.com for more details.

6 Testing the FMC+ Extender Cards

The FMC+ Extender Card has been designed to test low-speed signals and high-speed multi-gigabit transceivers on any FPGA development board or FPGA carrier card with the FMC+ interface.

6.1 Test Setup

General functional testing of power, control and low-speed signal are assumed with a successful power-up of the card. Key testing results are focused on verifying full-speed operation of the MGTs routed via the HSPC connectors.

To determine electrical performance of the FMC+ Extender Card, a Xilinx VCU118 was utilized as the FMC+ carrier along with the Samtec HSPC Loopback Card.




Figure 4 – FMC+ Extender Card Test Setup Utilizing the HSPC Loopback Card

6.2 Testing Results

The Test Setup ran over 24 channels and was found to be error free for over 15 hours of testing with a BER < 5.4e-14. The resulting data in Figure 5 and Figure 6.




Figure 5 – Eye Diagram for Test Setup 1

| | | | | | | | | | | | | | | | | | | |
|--|-------------|-------------|-------------|----------|-----|----------|-------|-------------|-------------|-----------------|-----------------|----------------|---|--------|-------|-------|------|--|
| Tcl Console Messages Serial IO Links Serial IO Scans | | | | | | | | | | | | | | | | | | |
| Name TX RX Status Bits Errors BER BERT Reset Tx Pattern Rx Pattern Tx Pre-Cursor Tx Post-Cursor Tx Diff Swing DFE Enabled Inject Error Tx Reset Rx Reset RX Lock | | | | | | | | | | | | | | | | | | |
| Found 13 | MGT_X0Y25TX | MGT_X0Y25RX | 28.000 Gbps | 1.856E13 | 0E0 | 5.35E-14 | Reset | PRBS 31-bit | PRBS 31-bit | 1.15 dB (00101) | 5.19 dB (10010) | 845 mV (10000) | ✓ | Inject | Reset | Reset | Lock | |
| Found 14 | MGT_X0Y26TX | MGT_X0Y26RX | 28.000 Gbps | 1.856E13 | 0E0 | 5.35E-14 | Reset | PRBS 31-bit | PRBS 31-bit | 1.15 dB (00101) | 5.19 dB (10010) | 845 mV (10000) | ✓ | Inject | Reset | Reset | Lock | |
| Found 15 | MGT_X0Y27TX | MGT_X0Y27RX | 28.000 Gbps | 1.856E13 | 0E0 | 5.35E-14 | Reset | PRBS 31-bit | PRBS 31-bit | 1.15 dB (00101) | 5.19 dB (10010) | 845 mV (10000) | ✓ | Inject | Reset | Reset | Lock | |
| Found 16 | MGT_X0Y28TX | MGT_X0Y28RX | 28.000 Gbps | 1.856E13 | 0E0 | 5.35E-14 | Reset | PRBS 31-bit | PRBS 31-bit | 1.15 dB (00101) | 5.19 dB (10010) | 845 mV (10000) | ✓ | Inject | Reset | Reset | Lock | |
| Found 17 | MGT_X0Y29TX | MGT_X0Y29RX | 27.971 Gbps | 1.856E13 | 0E0 | 5.35E-14 | Reset | PRBS 31-bit | PRBS 31-bit | 1.15 dB (00101) | 5.19 dB (10010) | 845 mV (10000) | ✓ | Inject | Reset | Reset | Lock | |
| Found 18 | MGT_X0Y30TX | MGT_X0Y30RX | 28.010 Gbps | 1.856E13 | 0E0 | 5.35E-14 | Reset | PRBS 31-bit | PRBS 31-bit | 1.15 dB (00101) | 5.19 dB (10010) | 845 mV (10000) | ✓ | Inject | Reset | Reset | Lock | |
| Found 19 | MGT_X0Y31TX | MGT_X0Y31RX | 28.000 Gbps | 1.856E13 | 0E0 | 5.35E-14 | Reset | PRBS 31-bit | PRBS 31-bit | 1.15 dB (00101) | 5.19 dB (10010) | 845 mV (10000) | ✓ | Inject | Reset | Reset | Lock | |
| Found 20 | MGT_X0Y32TX | MGT_X0Y32RX | 28.000 Gbps | 1.856E13 | 0E0 | 5.35E-14 | Reset | PRBS 31-bit | PRBS 31-bit | 1.15 dB (00101) | 5.19 dB (10010) | 845 mV (10000) | ✓ | Inject | Reset | Reset | Lock | |
| Found 21 | MGT_X0Y33TX | MGT_X0Y33RX | 28.000 Gbps | 1.856E13 | 0E0 | 5.35E-14 | Reset | PRBS 31-bit | PRBS 31-bit | 1.15 dB (00101) | 5.19 dB (10010) | 845 mV (10000) | ✓ | Inject | Reset | Reset | Lock | |
| Found 22 | MGT_X0Y34TX | MGT_X0Y34RX | 28.000 Gbps | 1.856E13 | 0E0 | 5.35E-14 | Reset | PRBS 31-bit | PRBS 31-bit | 1.15 dB (00101) | 5.19 dB (10010) | 845 mV (10000) | ✓ | Inject | Reset | Reset | Lock | |
| Found 23 | MGT_X0Y35TX | MGT_X0Y35RX | 27.987 Gbps | 1.856E13 | 0E0 | 5.35E-14 | Reset | PRBS 31-bit | PRBS 31-bit | 1.15 dB (00101) | 5.19 dB (10010) | 845 mV (10000) | ✓ | Inject | Reset | Reset | Lock | |

Figure 6 – Channel Results for Test Setup 1

7 Conclusions

FPGA carrier card developers require easy-to-use options to confirm the operation of the VITA 57.4 FMC+ expansion connector typically found on these platforms. In some cases, the mating height of the standard FMC+ connectors may prevent fully leveraging the connectivity options of all FMC+ modules.

The VITA 57.4 FMC+ Extender Card (REF-212564-01) has been designed for placement between FPGA Carrier Cards and FMC+ Modules. This increased space can be used for additional I/O expansion during development. The FMC+ Extender Card also provides a cost-effective option for extending the life of the FPGA Carrier Card HSPC connectors used as test platforms. It is ideal for benchtop testing, system debugging, probing, or FPGA development.

The card provides FPGA designers an easy to use option for testing low-speed interfaces and high-speed multi-gigabit transceivers on any FPGA development board or FPGA carrier card. It can run system data or BER testing on all channels in parallel. This makes evaluation and development with an FPGA much easier.

The FMC+ Extender Cards have been tested on numerous, popular FPGA evaluation kits and carrier cards. Data rates on the MGTs have been confirmed to 28 Gbps and beyond.

Additional details on can be found at www.samtec.com/kits.

SAMTEC USA

P.O. Box 1147 • New Albany, IN 47151-1147 USA
+1-800-SAMTEC-9 (+1-800-726-8329) USA & Canada
Tel: +1-812-944-6733 • Fax: +1-812-948-5047
Email: info@samtec.com

SAMTEC NORTHERN CALIFORNIA

2323 Owen St., Ste 120 • Santa Clara, CA 95054
+1-800-726-8329 (USA & Canada)
Tel: +1-812-944-6733 • Fax: +1-408-217-5171
Email: samtecsiliconvalley@samtec.com

SAMTEC SOUTHERN CALIFORNIA

5410 Trabuco Road • Suite 120 • Irvine, CA 92620
Tel: +55 31 9 9146 4447
Email: samtecsoutherncalifornia@samtec.com

SAMTEC SOUTH AMERICA

Rua Alagoas Nr 1460 • Sala 805 • Bairro Savassi
Belo Horizonte - Minas Gerais 30130-160 • Brazil
Tel: +55 31 9 9146 4447
Email: brazilsales@samtec.com

SAMTEC UNITED KINGDOM

11 Mollins Court • Westfield, Cumbernauld • Scotland G68 9HP
Tel: +44 01236 739292 • Fax: +44 01236 727113
Email: scotland@samtec.com

SAMTEC GERMANY

Streiflacher Str. 7 • 82110 Germering • Germany
+0800 SAMTEC9 (+0800 / 72 68 329) Germany only
Tel: +49 (0) 89 / 89460-0 • Fax: +49 (0) 89 / 89460-299
Email: germany@samtec.com

SAMTEC FRANCE

Val d' Europe Park • 11, rue du Courtalin - Bâtiment B
77700 Magny le Hongre • France
Tel: +33 1 60 95 06 60 • Fax: +33 1 60 95 06 61
Email: france@samtec.com

SAMTEC ITALY

Via Colleoni 25 • Centro Direzionale Colleoni
Palazzo Pegaso Ingresso 3
0864 Agrate Brianza-Monza Brianza (MB) • Italy
Tel: +39 039 6890337 • Fax: +39 039 6890315
Email: italy@samtec.com

SAMTEC NORDIC/BALTIC

Solkraftsvägen 25 • 13570 Stockholm • Sweden
Tel: +46 8 4477280 • Fax: +46 8 7420413
Email: scandinavia@samtec.com

SAMTEC BENELUX

11 Mollins Court • Westfield, Cumbernauld
Scotland G68 9HP
Tel: +44 01236 739292 • Fax: +44 01236 727113
Email: benelux@samtec.com

SAMTEC ISRAEL

21 Bar-Kochva St. • Concord Tower
B'nei Brak, Israel 51260
Tel: +972 3 7526600 • Fax: +972 3 7526690
Email: israel@samtec.com

SAMTEC INDIA

#11, 2nd Floor, Chetana, Dattatreya Road
Basavanagudi • Bangalore • 560 004 India
Tel: +91 80 2660 5303 • +91 73 3866 0600
Email: india@samtec.com

SAMTEC ANZ

2A San Antonio Court • Mentone 3194 • Victoria, Australia
Tel: +613 9580 0683 • Fax: +613 9580 0684
Email: australia@samtec.com

SAMTEC SINGAPORE

1 Kallang Sector #05-01/02 • Kolam Ayer Industrial Park
Singapore 349276
Tel: +65 6745 5955 • Fax: +65 6841 1502
Email: singapore@samtec.com

SAMTEC JAPAN

Nisso No. 16 Bldg. • 3-8-8, Shinyokohama, Kohoku-ku
Yokohama-shi, Kanagawa 222-0033 Japan
Tel: +81 45 475 1385 • Fax: +81 45 475 1340
Email: japan@samtec.com

SAMTEC CHINA

Room 608, Zone A, Hanghui Plaza • No 600 Yunjin Road
Shanghai, China 200232
Tel: +86 21 6057 2288 • Fax: +86 21 5423 4575
Email: china@samtec.com

SAMTEC TAIWAN

Room D, Floor B1, No. 205, Sec. 3 • Beixin Rd.
Xindian District • New Taipei City 23143 • Taiwan
Tel: +886 2 7727 4060 • Fax: +886 2 7727 4179
Email: taiwan@samtec.com

SAMTEC HONG KONG

Room 18, 13/F, Shatin Galleria • 18-24 Shan Mei Street
Fo Tan, Shatin, Hong Kong
Tel: +852 26904858 • Fax: +852 26904842
Email: hongkong@samtec.com

SAMTEC KOREA

#801, 8F, 10, Seongnam-daero 43beon-gil
Bundang-gu, Seongnam-si, Gyeonggi-Do • 13636 South Korea
Tel: +82 31 717 5685 • Fax: +82 70 7500 0246
Email: korea@samtec.com