



DESIGNED & DIMENSIONED IN MILLIMETERS[INCHES]








TABLE 1		
ITEM	COMPONENT	-GN
1	SUB ASSEMBLY	SUB-BNC7T-P-C-GN-RA-CA6
2	FERRULE	BNC-FER-001-N
3	CAP	BNC7T-P-C-N-RA-CA6-CAP

NOTES:

- 1. \(\bigcirc\) REPRESENTS A CRITICAL DIMENSION.
- 2. PUSHOUT FORCE FOR CENTER CONTACT: 26.69N [6LBS] MIN.
- 3. SEE SHEET 3 FOR TERMINATION INFORMATION.
- 4. NOTE DELETED.
- 5. PRODUCT TO BE PACKAGED PER PACKAGING STANDARD CO-HD-WI-3040-M.
- 6. Rohs Compliant.
- 7. NOTE DELETED
- 8. NOTE DELETED

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN MILLIMETERS (INCHES)
TOLERANCES ARE:

DECIMALS ANGLES
.X: ±0.3 [.01] 5 °
.XX: ±0.13 [.005]
.XXX: ±0.051 [.0020]

PROPRIETARY NOTE

THIS DOCUMENT CONTAINS INFORMATION CONFIDENTIAL AND PROPRIETARY TO SAMTE, INC. AND SHALL NOT BE REPRODUCED OR TRANSFERRED TO OTHER DOCUMENTS OR DISCLOSED TO OTHERS OR USED FOR ANY PURPOSE OTHER THAN THAT WHICH IT WAS OBTAINED WITHOUT THE EXPRESSED WRITTEN CONSENT OF SAMTEC, INC.

MATERIAL: DO NOT SCALE DRAWING SHEET SHELL, FERRULE, NUT, CAP: BRASS

CONTACT: BRASS DIELECTRIC: PTFE GASKET: SILICONE



520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322

DESCRIPTION:

TRUE 75 OHM, BNC RA RG6 CABLE PLUG

BNC7T-P-C-XX-RA-CA6

BY: G. HERMAN 01/09/2009 | SHEET 1 OF 2

F:\DWG\MISC\MKTG\BNC7T-P-C-XX-RA-CA6-MKT.SLDDRW

