
REVISION CJ

DO NOT SCALE FROM THIS PRINT

TABLE 1					
"A"	CONTACT				
0.090 [2.29]	C-79-01-X				
N/A	C-79-53-X				
NI/A	C-79-53-X				
IN/A	C-79-12-X				
	C-79-53-X				
N/A	C-79-12-X				
	C-79-12-X				
0.600 [15.24]	C-79-02-X				
-03 0.208 [5.28]					
	"A" 0.090 [2.29] N/A N/A N/A 0.600 [15.24]				



SQT-120-01-XX-6 SHOWN

No OF POSITIONS -02 THRU -50 (PER ROW) -Ò1 (SEE NÓTE 3) LEAD STYLE (SEE TABLE 1)

SQT-1XX-XX-XXX-X-XXX

PLATING SPECIFICATION

.0787 [2.000]

REF (TYP)

- -F: 3µ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- -L: 10u" SELECTIVE GOLD IN CONTACT AREA. MATTE TIN ON TAIL.
- -G: 20µ" SELECTIVE GOLD IN CONTACT AREA, 3µ" SELECTIVE GOLD ON TAIL.
- -S: 30µ" SELECTIVE GOLD IN CONTACT AREA, MÄTTE TIN ON TAIL
- -H: 50µ" SELECTIVE GOLD IN CONTACT AREA, 3µ" SELECTIVE GOLD ON TAIL.
- -FM: '3µ" SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- -LM: 10µ" SELECTIVE GOLD IN CONTACT AREA, MÄTTE TIN ON TAIL.
- -SM: 30µ" SELECTIVE GOLD IN CONTACT AREA MÄTTE TIN ON TAIL.
- -STL: 30u" SELECTIVE GOLD IN CONTACT AREA. SnPb ON TAIL.

* = NOT RELEASED FOR PRODUCTION

** = MW OPTION, DO NOT DESIGN IN, SAMTEC WILL ONLY SUPPORT EXISTING BUSINESS 02/06/2002

POLARIZATION OPTION

-XXX: INDICATES POSITION

(-01 LEAD STYLE, ROWS -S, -D, -T ONLY)

(AVAILABLE ON -S, -D, -T ONLY)

**-MW: METAL WASHER (SHT 2, SEE FIG 4)

(NOT AVAILABLE ON -0, -5 & -6 ROWS) (SINGLE, DOUBLE, TRIPLE ROW: SEE FIG 2, SHT 2) *-SD1: SOLDER DONUT (SEE FIG 3, SHT 2)

(AVAILABLE ON LEAD STYLES -01 & -03 ONLY)

(5 POS MIN, 30 POS MAX, .300 MAX TAIL)

(SEE NOTE 10)

OPTION

ROW SPECIFICATION

-S: SINGLE (USE SQT-61-S)

-T: TRIPLE (USÈ SQT-62-T)

-D: DOUBLE (USE SQT-62-D)

-Q: QUAD (USE SQT-62-Q)

-5: FIVE ROW (USE SQT-62-5)

-6: SIX ROW (ÚSE SQT-62-6)

-RA: RIGHT ANGLE




TABLE 3					
ROW SPEC.	BODY	"B"			
-S	SQT-61-S	0.0787 [2.000]			
-D	SQT-62-D	0.1575 [4.000]			
-T	SQT-62-T	0.2362 [6.000]			
-Q	SQT-62-Q	0.3150 [8.000]			
-5	SQT-62-5	0.3937 [10.000]			
-6	SQT-62-6	0.4724 [12.000]			

NOTES:

- 1. (C) REPRESENTS A CRITICAL DIMENSION. 2. MINIMUM CONTACT RETENTION: .5 LB
- 3. -01 POSITION OFFERED FOR SINGLE ROW& ONLY FOR -S, -D, & -T ROWS RIGHT ANGLE ONLY.
- 4. SEE TABLE 2, SHEET 3 FOR PACKAGING
- 5. STOCK 62 POSITION FOR -D AND 61 POSITION FOR
- -S, -01 LEAD STYLE ONLY. TO BE CUT TO POSITION FOR CUSTOMER.
- 6. MAXIMUM BURR: .005[0.13]
 7. ENDWALL AFTER CUTTING: .031[.79]+/-.004[0.10], VOIDS MAY BE PRESENT. CONTACTS MUST NOT BE VISIBLE THROUGH THE ENDWALL
- 8. MAXIMUM CUT FLASH: .020[0.50]
- 9. MAXIMUM HEIGHT VARIATION: .005[0.13]
- 10. INSERT PK-07-N INTO SPECIFIED POSITION AND BREAK OFF TAB.

01 02

(POSITON PATTERN SINGLE ROW ONLY)

UNLESS OTHERWISE SPECIFIED. DIMENSIONS ARE IN INCHES. TOLERANCES ARE:

DECIMALS **ANGLES** .XX: ±.01 [.3] .XXX: ±.005 [.13] 2° .XXXX: ±.0020 [.051]

THIS DOCUMENT CONTAINS CONFIDENTIAL AND MANUFACTURING REPRODUCTION USE PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR

PROPRIETARY NOTE

REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC INC

DO NOT SCALE DRAWING SHEET SCALE: 2:1 INSULATOR: LCP, UL 94 VO, COLOR: BLACK CONTACT: PHOS BRONZE

MAX BOW ALLOWED: .004[.10] IN/IN

F:\DWG\MISC\MKTG\SQT-1XX-XXX-XXXX-XXXX-MKT.SLDDRW




520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com

DESCRIPTION

2MM SOCKET STRIP ASSEMBLY

SQT-1XX-XX-XXX-X-XXX

BY: BRATCHER 07/24/1995 | SHEET 1 OF 3



** -MW OPION, DO NOT DESIGN IN. SAMTEC WILL

ONLY SUPPORT EXISTING BUSINESS 2/06/02.


SCALE 6:1

Sycial State Scale: 2:1

Sycial Sycial State State: 2:1

Sycial Syci

PACKAGING VIEWS






SQT-1XX-01-XX-D (SEE TABLE 2)







SQT-1XX-02-XX-D (LOCATE PLUG AS SHOWN) (SEE TABLE 2)







SQT-1XX-01-XX-D-RA SHOWN (LOCATE PLUG AS SHOWN) (SEE TABLE 2)







SQT-1XX-05-XX-X (LOCATE PLUG AS SHOWN) (SEE TABLE 2)





SQT-1XX-03-XX-6 SHOWN (SEE TABLE 2)

\subset					=
	н	н	н	н	╢
Ш					

TABLE 2				
ROW SPEC.	No. OF POS	PKG TUBE	TUBE PLUG	
-03-S	04-50	PT-SQT001	TP-12	
-02-S	04-50	PT-1-24-10-03	TP-03	
-01-S-RA	04-50	PT-1-24-01-43	TP-24	
-01-D	04-50	PT-1-24-01-22	TP-03	
-02-D	04-50	PT-1-24-01-34	TP-07	
-03-D	04-50	PT-1-24-01-22	TP-03	
-01-D-RA	04-50	PT-1-24-01-45	TP-03	
-01-T	04-50	PT-1-24-05-09	TP-07	
-02-T	04-50	PT-1-24-01-102	TP-07	
-03-T	04-50	PT-1-24-08-15	TP-07	
-01-Q	04-50	PT-1-24-15-29	TP-07	
-02-Q	04-50	PT-1-24-02-51	TP-13	
-03-Q	04-50	PT-1-24-16-29	TP-07	
-01-T-RA	04-50	PT-1-24-06-40	TP-07	
-01-S	04-50	PT-SQT001	TP-12	
-03-5	15-50	PT-1-24-01-08	TP-13	
-02-5	15-50	PT-1-24-01-56	TP-31	
-01-6	ALL	PT-1-24-01-52	TP-07	
-02-6	ALL	PT-1-24-02-74	TP-25	
-03-6	ALL	PT-1-24-01-08	TP-13	
-01-5	15-50	PT-1-24-09F-109	TP-07	
-01-5, -02-5, -03-5	-02 THRU -14	LAYER PACKAGING		
-S, -D, -T, -Q	-01,-02, -03	LAYER PACKAGING		



SQT-1XX-03-XX-S SHOWN (SEE TABLE 2)

PROPRIETARY NOTE THIS DOCUMENT CONTAINS CONFIDENTIAL AND

PROPRIETARY INFORMATION AND ALL DESIGN,
MANUFACTURING, REPRODUCTION, USE, PATENT RIGHTS AND SALES RIGHTS ARE EXPRESSLY RESERVED BY SAMTEC, INC. THIS DOCUMENT SHALL NOT BE DISCLOSED, IN WHOLE OR PART, TO ANY UNAUTHORIZED PERSON OR ENTITY NOR REPRODUCED, TRANSFERRED OR INCORPORATED IN ANY OTHER PROJECT IN ANY MANNER WITHOUT THE EXPRESS WRITTEN CONSENT OF SAMTEC, INC.

DO NOT SCALE DRAWING

SHEET SCALE: 1:1



520 PARK EAST BLVD, NEW ALBANY, IN 47150 PHONE: 812-944-6733 FAX: 812-948-5047 e-Mail info@SAMTEC.com code 55322

DESCRIPTION:

2MM SOCKET STRIP ASSEMBLY

SQT-1XX-XX-XXX-X-XXX BY: BRATCHER 07/24/1995 | SHEET 3 OF 3