

REV CR

NOTE: "R" = USED MEASURED DIMENSION (REF)
 "S" = $\{ ("R" - .1969 [5.000]) / 2 \} \pm .020 [.51]$

FIG 5
 -K: POLYIMIDE FILM
 (DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)







FIG 6
 -SL: SOLDER LOCK
 (DIFFERENT AS SHOWN, OTHERWISE SAME AS FIG 1)

TSM-XX-DHU-XX-SL

DIMENSIONS ARE IN INCHES		UNLESS OTHERWISE NOTED		TOLERANCES ARE		TITLE:	DWG NO:
ONE PLACE DECIMALS ± .1 [3]	TWO PLACE DECIMALS ± .01 [3]	THREE PLACE DECIMALS ± .005 [13]	FOUR PLACE DECIMALS ± .0020 [65]	ANGLES	± 2°	TERMINAL STRIP DOUBLE SURFACE MOUNT	TSM-1XX-XX-XXX-XX-XXX-XX SHEET 2 OF 3



IN-PROCESS 1



IN-PROCESS 2




FIG 4
 -MT: MIXED TECHNOLOGY
 (DIFFERENT AS SHOWN,
 OTHERWISE SAME AS FIG 1)

• PROPRIETARY INFO •
 ALL RIGHTS RESERVED
 SAMTEC CORPORATION
 520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
 PHONE (812) 944-8733 P.O. BOX 1147
 CODE 95322

MISC\MKTG
 TSM-1XX-XX-XXX-XX-XXX-XX-MKT2

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
 PHONE (812) 944-8733 P.O. BOX 1147
 CODE 95322

MADE BY: BRATCHER 7-27-95 TSM-1XX-XX-XXX-XX-XXX-XX
 SHEET 2 OF 3