

Series: SEAM/SEAF

Description: Open Pin Field Array, 1.27mm x 1.27mm Pitch, 7 mm Stack Height

Connector Overview

SEAM/SEAF is a 1.27mm x 1.27mm pitch interconnects system for elevated high-speed board-to-board applications. The open pin field design allows for both single-ended and differential pair signaling to be employed. The SEAM/SEAF Series is available in 4, 5, 6, 8, and 10 row open pin field arrays. Pins per row selections are 20, 30, 40, or 50. This report reflects only the hi-speed electrical characteristics specific to a mated 7mm stack height SEAM/SEAF test system.

Connector System Speed Rating

SEAM/SEAF Series, 1.27mm x 1.27mm (.050" x .050") pitch interconnect,
7 mm Stack Height.

<u>Signaling</u>	<u>Speed Rating</u>
Single-Ended: 1:1 S/G	12.5 GHz/ 25Gbps
Single-Ended: 2:1 S/G	12.5 GHz/ 25Gbps
Differential: Optimal Horizontal	13 GHz/ 26Gbps
Differential: Optimal Vertical	13 GHz/ 26Gbps
Differential: High Density Vertical	12.5 GHz/ 25Gbps

The Speed Rating is based on the -3 dB insertion loss point of the connector system. The -3 dB point can be used to estimate usable system bandwidth in a typical, two-level signaling environment.

To calculate the Speed Rating, the measured -3 dB point is rounded up to the nearest half-GHz level. The up rounding corrects for a portion of the test board's trace loss, since a short length of trace loss is included in the loss data in this report. The resulting loss value is then doubled to determine the approximate maximum data rate in Gigabits per second (Gbps).

For example, a connector with a -3 dB point of 7.8 GHz would have a Speed Rating of 8 GHz/ 16 Gbps. A connector with a -3 dB point of 7.2 GHz would have a Speed Rating of 7.5 GHz/15 Gbps.