



70 GHz ASSEMBLIES

| BE70A | TRANSMISSION TYPE | END 2 | PHASE MATCHING | ROW OPTION | POSITIONS PER ROW | OVERALL LENGTH |
|-------|---|--|--|--|--|--|
| | -S = Stripline -M = Microstrip | -18SJ = 1.85 mm Straight Jack -18SP = 1.85 mm Straight Plug | -2 = 2.0 Pico-seconds -5 = 5.0 Pico-seconds -N = No Phase Matching | -1 = Single Row (-02, -04, -08 & -12 positions only) -2 = Double Row (-03 through -16 positions only) | -02, -03, -04, -06, -08, -10, -12, -14, -16 | "XXXX" = Overall length in millimeters -0152 (152 mm) 5.984" minimum |

| | |
|------------------|--------------------|
| DC TO | PAM 4 |
| 70 GHz | 112 Gbps |

BE70A
End 2 Connectors:
1.85 mm (70 GHz)



50 GHz & 40 GHz ASSEMBLIES

| BE40A | TRANSMISSION TYPE | END 2 | PHASE MATCHING | 2 | POSITIONS PER ROW | OVERALL LENGTH |
|-------|---|--|--|---|---|--|
| | -S = Stripline -M = Microstrip | -92SJ = 40 GHz, 2.92 mm Straight Jack -24SJ = 50 GHz, 2.40 mm Straight Jack -92SP = 40 GHz, 2.92 mm Straight Plug -24SP = 50 GHz, 2.40 mm Straight Plug | -2 = 2.0 Pico-seconds -5 = 5.0 Pico-seconds -N = No Phase Matching | | -03, -04, -06, -08, -10, -12, -14, -16 | "XXXX" = Overall length in millimeters -0152 (152 mm) 5.984" minimum |

| | |
|------------------|-------------------|
| DC TO | PAM 4 |
| 50 GHz | 56 Gbps |

BE40A
End 2 Connectors:
2.40 mm (50 GHz)
2.92 mm (40 GHz)

