




THROUGH-HOLE LOW-PROFILE HEADER



(2.00 mm) .0787" PITCH • A-TMM SERIES

A-TMM

Board Mates:

A-CLT, A-SQT, A-SQW,
A-ESQT, A-SMM, A-MMS

SPECIFICATIONS

Insulator Material:

Black Liquid Crystal Polymer

Terminal Material:

Phosphor Bronze

Plating:

Sn or Au over
50 μ" (1.27 μm) Ni

Current Rating (A-SMM/A-TMM):

3.2 A per row
(2 pins powered)

Operating Temp Range:

-55 °C to +105 °C with Tin;
-55 °C to +125 °C with Gold

Voltage Rating:

281 VAC mated with A-SQW;
250 VAC mated with A-SQT

PROCESSING

Lead-Free Solderable:

Yes

ALSO AVAILABLE

Other plating
(MOQ Required)



02 thru 50






Specify
LEAD
STYLE
from
chart

-L
= 10 μ" (0.25 μm)
Gold on post,
Matte Tin on tail

-T
= Matte Tin

-S
= Single
Row
-D
= Double
Row

**-RA &
-RE**
= Right-angle
(Lead Style
-01 only)
(2 positions
minimum)



LEAD STYLE	A	B	C
-01		(3.20) .126	(3.50) .138
-02	(8.20) .323	(3.70) .146	(3.00) .118
-03		(4.00) .158	(2.70) .106
-04	(5.69) .224	(1.91) .075	(2.29) .090
-05	(5.43) .214	(1.65) .065	
-06	(9.58) .377	(3.20) .126	(4.88) .192



Note:

Some lengths, styles and options are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

samtec.com/Automotive

A-221