

tube

OPTICAL MICRO FLYOVER SYSTEM™

| ECUO - | WIDTH | DATA RATE | CABLE LENGTH | - 0 - HEAT - 1 | FIBER TYPE | END 2 OPTIONS |
|--------|---|---|---|---|--|--|
| | -B04 = 4 Tx + 4 Rx -T12 = 12 Tx -R12 = 12 Rx -Y12 | -14 = 14 Gbps per lane -16 = 16.1 Gbps per lane (N/A -B04) -25 | -"XXX" = Overall Length in Centimeters | -1 = Flat -2 = Pin-fin (-14 & -16 only) -3 = Flat with | -4 = Aqua loose tube with boot -5 = Jacketed ribbon with boot | (Leave blank for -U12) -Y12 requires -2X end option 12 Fibers -01 = MTP® Male -02 = MTP® Female -07 = MXC® Internal Plug* -0E = MPO Plus®, |
| ECUO | = 12 Tx + 12 Rx -U12 = 12 Channel AOC (Unidirectional) | = 25.7 Gbps per lane -28 = 28.1 Gbps per lane (-B04 only) | | groove -4 = PCle® Pin-fin (-14 & -16 only) -5 = 1.75 cm tall Pin-fin | -6 = Jacketed ribbon -7 = Black loose tube with boot -8 = Black | Male, bayonet 24 Fibers -21 = MTP® Male -22 = MTP® Female -27 = MXC® Internal Plug* -2E = MPO Plus®, Male, bayonet |

ECUO Mates with: UEC5, UCC8, **OPA**



FEATURES

- Supports data center and HPC protocols, including: Ethernet, InfiniBand $^{\mathbb{N}}$, Fibre Channel
- Customizable optical connectors
- · Integrated coupling capacitors
- Standard temperature range 0 °C to +70 °C
- Evaluation & Development boards available

CLASS 1 LASER PRODUCT per IEC 60825-1 Ed. 3 (2014)

Applies to all end 2 options except MXC®

TOOLING


Insertion Tool: CAT-IN-ECUO-02

Notes: MTP® is a registered trademark of US Conec Ltd.


PCI-SIG®, PCI Express® and PCle® design marks are registered trademarks and/or service marks of PCI-SIG.

All FireFly™ designs, specifications and components are preliminary and subject to change without notice.

Some lengths, styles and options are non-standard. non-returnable.




(-B04 only)



-2 PIN-FIN HEAT SINK

-07 (MXC® INTERNAL PLUG SHOWN)



-3 FLAT WITH GROOVE HEAT SINK (MULTI-ROW CONFIGURATION)

*CLASS 3R LASER PRODUCT

Laser Radiation. Avoid Direct Eye Exposure.



ACAUTION LASER 3R



Applies to MXC® end option only.

View complete specifications at: samtec.com?ECUO