

NITROWAVE™ CABLE TECHNOLOGY

HIGH-PERFORMANCE, PHASE & AMPLITUDE STABLE

DC TO
110
GHz

Samtec's new **Nitrowave™ Phase & Amplitude Stable RF Cable** offers improved stability with flexure. The coaxial structure – with an outer jacket colored in **distinctive Samtec orange** – is designed to meet the demands of aerospace, defense, datacom, computer/semiconductor, and instrumentation markets. Performance is optimized at frequencies beyond traditional industry targets to support emerging applications.


NITROWAVE™ CABLE TECHNOLOGY

- High-performance, low-loss microwave cable assemblies
- Phase and amplitude stable with flexure
- Consistent contact resistance between layers
- Lower density dielectric minimizes loss
- State-of-the-art shielding techniques and Dynamic Performance Layer (DPL)
- Silver plating enhancements mitigate corrosion potential
- Electrical performance optimized at next gen frequencies (GHz): 18, 32, 43.5, 71, 95, 110
- Mechanical and environmental robustness
- Typical phase vs. temp & power handling
- For armored cable versions for crush, torque and pull resistance, contact RFGroup@samtec.com



Series	LL018	LL032	LL043*	LL071	LL095	LL110
Impedance (Ω)	50					
Max Frequency (GHz)	18	32	43.5	71	95	110
Outer Dia. (inches)	0.309	0.182	0.141	0.094	0.076	0.068
Min Static Bend Radius	1.25	0.375	0.25	0.125	0.156	0.156
Velocity of Propagation (%)	77					
Min Shielding Effectiveness (dB)	-90					
Temp Range (°C)	-65 °C to +125 °C					
Insertion Loss	See Maximum IL Chart					
End 1/End 2	1.00 mm, 1.35 mm, 1.85 mm, 2.40 mm, 2.92 mm, SMPM, SMP, SMA, N Type, TNCA					

MAXIMUM INSERTION LOSS (dB/m)



HIGH-PERFORMANCE MICROWAVE CABLE


Cable Assemblies LL032



FEATURES

Impedance:
50 Ω
Outer Diameter:
0.182"
Bend Radius:
0.375"
Velocity of Propagation:
77 %
Min. Shielding Effectiveness:
-90 dB
Temp Range:
-65 °C to +125 °C

SERIES	END 1 CONNECTOR	END 2 CONNECTOR	OVERALL LENGTH	PHASE MATCHING	PHASE MATCHING CABLES
LL032 = High-Performance Cable to 32 GHz	Specify END OPTION from chart		-"XXXX" = Overall Length in millimeters -0100 (100 mm) 3.94" min.	Leave blank for no phase matching -1 = 1 Pico Second -2 = 2 Pico Seconds -5 = 5 Pico Seconds	Leave blank for 1 cable. (Only available with no phase matching option) -02 to 16 = No. of cables



LL032-92SP-92SP-XXXX-X-XX

END OPTION	INTERFACE TYPE	GENDER	MAXIMUM RETURN LOSS (PER END)	MAXIMUM VSWR (PER END)	FREQUENCY
-92SP	2.92 mm	PLUG	21.53	1.183	DC TO 32 GHz

Cable Assemblies LL018




FEATURES

Impedance:
50 Ω
Outer Diameter:
0.309"
Bend Radius:
1.25"
Velocity of Propagation:
77 %
Min. Shielding Effectiveness:
-90 dB
Temp Range:
-65 °C to +125 °C

SERIES	END 1 CONNECTOR	END 2 CONNECTOR	OVERALL LENGTH
LL018 = High-Performance Cable to 18 GHz	Specify END OPTION from chart		-"XXXX" = Overall Length in millimeters -0100 (100 mm) 3.94" minimum

PRELIMINARY



LL018-01SP-01SP-XXXX

END OPTION	INTERFACE TYPE	GENDER	MAXIMUM RETURN LOSS (PER END)	MAXIMUM VSWR (PER END)	FREQUENCY
-01SP	SMA	PLUG	22.51	1.162	DC TO 18 GHz