

EXTENDED TEMP OPTICAL MICRO FLYOVER SYSTEM™




ETUO	WIDTH	DATA RATE	CABLE LENGTH	0	HEAT SINK	1	FIBER TYPE	END 2 OPTIONS
	-B04 = 4 Tx + 4 Rx -T12 = 12 Tx -R12 = 12 Rx -Y12 = 12 Tx + 12 Rx -U12 = 12 Channel AOC (Unidirectional)	-10 = 10.3125 Gbps -25 = 25.7 Gbps (-B04 only)	-“XXX” = Overall Length in Centimeters		-1 = Flat -2 = Pin-fin -3 = Flat with groove -4 = PCIe® Pin-fin (-10 only) -5 = 1.75 cm tall Pin-fin (-B04 only)		-5 = Jacketed ribbon with boot -6 = Jacketed ribbon -7 = Black loose tube with boot -8 = Black loose tube	(Leave blank for -U12 or -B04 width) -Y12 requires -2X end option 12 Fibers -01 = MTP® Male -02 = MTP® Female -07 = MXC® Internal Plug* -0A = VITA™ 66.1/66.4 READY -0C = MT38999 Male -0E = MPO Plus®, Male, bayonet 24 Fibers -21 = MTP® Male -22 = MTP® Female -27 = MXC® Internal Plug* -2A = VITA™ 66.1/66.4 READY -2C = MT38999 Male -2E = MPO Plus®, Male, bayonet

ETUO

Mates with:
UEC5, UCC8,
OPA

FEATURES

- Optimized for SWaP
- Extended temperature range from -40 °C to +85 °C
- Micro rugged board level connector system with positive latching, weld tabs and loading guides for secure connection
- Pigtailed cable for maximum link budget
- Customizable optical connectors
- Integrated coupling capacitors
- Integral heat sink provides optimal cooling for thermal operating conditions
- Evaluation and Development boards available



Notes:

All FireFly™ designs, specifications and components are preliminary and subject to change without notice.

MTP® and MXC® are registered trademarks of US Conec Ltd.

PCI-SIG®, PCI Express® and the PCIe® design marks are registered trademarks and/or service marks of PCI-SIG.


VITA/VNX/VNX+/FMC/FMC+/XMC/XMC+ are all respective trademarks of VITA

Some lengths, styles and options are non-standard, non-returnable.

CLASS 1 LASER PRODUCT
per IEC 60825-1 Ed. 3 (2014)

Applies to all end 2 options except MXC®

***CLASS 3R LASER PRODUCT**
Laser Radiation. Avoid Direct Eye Exposure.



Applies to MXC® end option only.

View complete specifications at: samtec.com?ETUO