

50 Ω MCX TO 6 GHz

MCX Cable Assemblies RF174, RF178, RF316, **RS316**



SERIES

END 1 CONNECTOR

END 2 CONNECTOR

OVERALL LENGTH

RF174

= RG 174 Cable

RF178

= RG 178 Cable

RF316

= RG 316 Cable, Single Braid Shield

RS316

= RG 316 Cable, Double Shielded

-02SJ1

= MCX Straight Jack

-02RP1

= MCX Right-angle Plug (RS316 not available)

-02SP1

= MCX Straight Plug

"XXXX"

= Overall Length in millimeters

-0100 (100 mm) 3.94" minimum

ALSO AVAILABLE

50 Ω: MMCX, SMA, SMB, BNC, TNC, N Type = RF174, RF178, RF316 50Ω : MMCX, SMA, BNC, TNC = RS316

MCX Board Connectors MCX-TH, MCX-SM, MCX-EM, MCX-MT

Cable Mates: RF174, RF178, RF316, RS316, GRF1H-C, IJ5H



MCX

GENDER TYPE

-P

= PCB = Jack Mount -P

= Plug

(6.00)

-ST-SM1

(Jack)

PLATING

-H = 30 µ" (0.76 µm) Gold center contact, 3 μ" (0.08 μm) Gold outer contact

-ST = Straight

ORIENTATION

-RA = Right-angle

(9.50)

-TH2

TERMINATION

-TH1

= Through-hole (-ST plug not available)

= Elevated Through-hole (-ST plug only)

-SM1

= Surface Mount (Jack only)

-EM1

= Edge Mount (–ST jack only)

-MT1

Mixed Technology (-ST jack only)

MCX Cable Connectors MCX-CA



CONNECTORS FOR INDUSTRY STANDARD CABLES		
MCX-J-C-H-ST-CA1	RG 174/316 Cable	
*MCX-J-C-H-ST-CA2	RG 178 Cable	
MCX-J-C-HF-ST-CA1S	RG 316 Double Shielded Cable	
*MCX-P-C-H-ST-CA1	RG 174/316 Cable	
MCX-P-C-H-ST-CA2	RG 178 Cable	
MCX-P-C-HF-ST-CA1S	RG 316 Double Shielded Cable	
*MCX-P-C-H-RA-CA1	RG 174/316 Cable	
MCX-P-C-H-RA-CA2	RG 178 Cable	

P-C = Cable Plug J-C = Cable Jack

-(10.60) .417 -

-RA-TH1

(Plug)


H or HF = Plating (30 μ" Gold center contact, 3 μ" Gold outer contact)

ST = Straight

RA = Right-angle

(5,00) 197 SQ	4 (3,70) 1,146 DIA	
	-RA	





-P-ST

TYPE (-RA)	A	В
-P-CA1	(7.78) .306	(9.50) .374
-P-CA2	(8.58) .338	(10.00) .394

TYPE (-ST)	E	F
-J-CA1	(4.50) .177	(15.50) .610
-J-CA2	(4.78) .188	(15.00) .591
-J-CA1S	(4.50) .177	(15.50) .610