# **mPOWER**<sup>®</sup>

ULTRA MICRO POWER SYSTEM

(2.00 mm) .0787" PITCH



18 A m p s

> 17.5 A 16.3 A

> 13.9 A

13.2 A

8.9 A

#### **FEATURES & BENEFITS**

- Board-to-board, cable-to-board and cable-to-cable
- Up to 18 A per blade (1 blade powered)
- Choice of 2 to 10 positions
- 5 mm to 20 mm stack heights; vertical and right-angle orientations
- Tin or 10  $\mu$ " Gold plated power blades; 30  $\mu$ " Gold plating available to meet specific regulations
- Optional weld tabs
- Mating cable assemblies with plastic top or metal side latching
- Severe Environment Testing qualified (UMPT/UMPS); aligns with MIL-DTL-55302. Visit samtec.com/set

### CREEPAGE & CLEARANCE

PINS 1

2

3

4

10

allowable temperature.

UMPT/UMPS					
CREEPAGE	2.20 mm				
CLEARANCE	1.65 mm				

CURRENT RATING (PER CONTACT)

UMPT/UMPS

17.8 A

15.5 A

13.5 A

12.9 A

9.8 A

Ratings are derated 20% with 30 °C rise to maximum


Selectively loading contacts achieves customer specific creepage and clearance requirements.

#### **KEY SPECIFICATIONS (UMPT/UMPS)**

STACK HEIGHTS	INSULATOR MATERIAL	CONTACT MATERIAL	PLATING	OPERATING TEMP RANGE	VOLTAGE RATING	LEAD-FREE SOLDERABLE
5, 6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 18, 20 mm	Black LCP	Copper Alloy	Sn or Au over 50 μ" (1.27 μm) Ni	-55 °C to +105 °C with Tin -55 °C to +125 °C with Gold	460 VAC/ 650 VDC	Yes

## **mPOWER**°

#### **ULTRA MICRO POWER CABLE**



#### **TOOLING**

Hand Tool: CAT-HT-489-1618-13 Note:

Mini Applicator: CAT-MC-489-1618-XX-01

0

 $\oplus$ 

Some lengths, styles and options are non-standard, non-returnable.

View complete specifications at: samtec.com?IMPC & samtec.com?CC489

-М