

(0.635 mm) .025" PITCH • QTS/QSS SERIES

QTS Board Mates:

OSS

QSS **Board Mates:** OTS

QTS/QSS

Cable Mates: SQCD

Standoffs:

SO

SPECIFICATIONS

Insulator Material: Liquid Crystal Polymer Contact Material: Phosphor Bronze Plating: Au or Sn over 50 μ" (1.27 μm) Ni Current Rating: Contact: 1.8 A per pin (2 pins powered) Ground Plane: Ground Flane:
23.1 A per ground plane
(1 ground plane powered)
Operating Temp Range:
-55 °C to +125 °C
Voltage Rating:
285 VAC

Max Cycles: 100

NO. OF POSITIONS PER ROW QTS

> -025, -050, -075 (50 total positions per bank)

Specify LEAD **STYLE** from Chart

LEAD

STYLE

PLATING OPTION

-F = Gold flash on contact. Matte Tin on tail

= 10 μ" (0.25 μm) Gold on contact, Matte Tin on tail

-C = 50 μ" (1.27 μm) Electro-Polished Selective Gold on contact, Matte Tin on tail (passes 10 year MFG testing)

-K = (7.00 mm) .275" DIA Polyimide film Pick & Place Pad

OTHER OPTIONS


Leave blank for Tray Packaging

"X"R

-TR

= Tape & Reel

-FR = Full Reel Tape & Reel must order max. quantity per reel; contact Samtec for quantity breaks)







QTS LEAD STYLE	A	MATED HEIGHT WITH QSS
-01	(4.27) .168	(5.00) .197
-02	(7.26) .286	(8.00) .315

*Processing conditions will affect mated height. See SO Series for board space tolerances.

View complete specifications at: samtec.com?QTS

PROCESSING

Lead-Free Solderable:

QTS SMT Lead Coplanarity: (0.10 mm) .004" max

QSS SMT Lead Coplanarity: (0.10 mm) .004" max

(025-050) (0.15 mm) .006" max (075)* *(.004" stencil solution may be available; contact

ipg@samtec.com)
Board Stacking:

For applications requiring more than two connectors contact ipg@samtec.com



Note:

Some lengths, styles and options are non-standard, non-returnable.



-025, **-050, -075** (50 total positions per bank)

= Gold flash on contact, Matte Tin on tail

-L = 10 μ" (0.25 μm) Gold on contact, Matte Tin on tail

-C = 50 μ" (1.27 μm) Electro-Polished Selective Gold on contact, Matte Tin on tail (passes 10 year MFG testing)


-GP = Guide Holes for mating with QTS-RA

-K = (8.25 mm) .325' DIA Polyimide Film Pick & Place Pad

Leave blank for Tray Packaging

> -TR = Tape & Reel

-FR = Full Reel Tape & Reel must order max. quantity per reel; contact Samtec for quantity breaks)



(No. of Positions per Row/25) (20.00) .7875 + (10.90) .429 \oplus \oplus (No. of Positions per Row/25) x (20.00) .7875 + (5.72) .225 -GP OPTION

View complete specifications at: samtec.com?QSS